

Engineering Development Model

Frequency Mixer

ADE-ED12873/11

Level 13 (LO Power +13 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CD542

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	10		1500	MHz
	RF (fL to fU)	10		1500	MHz
	IF	10		1000	MHz
Conversion Loss	Mid Band		6.9		dB
	Total Range		7.1		dB
LO-RF Isolation	Low Range		62		dB
	Mid Range		52		dB
	Upper Range		38		dB
LO-IF Isolation	Low Range		50		dB
	Mid Range		39		dB
	Upper Range		29		dB
IP3 Input			+18.71		dBm

Note: Low Range = [fL to 10fL] Mid Range = [10fL to fU/2] Upper Range = [fU/2 to fU]
mid band = [2fL to fU/2]

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
LO	6
RF	3
IF	2
GROUND	1, 4, 5