

Frequency Mixer

ADE-ED13321/1

Level 17 (LO Power + 17 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CD542

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (f _L to f _U)	10		1790	MHz
	RF (f _L to f _U)	10		1790	MHz
	IF	10		470	MHz
Conversion Loss	Total Range		7.6		dB
LO-RF Isolation			39		dB
LO-IF Isolation			39		dB
Input IP3			+27		dBm
1dB Compression			+15		dBm

MAXIMUM RATINGS	
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C

PIN CONNECTIONS	
LO	6
RF	3
IF	2
GROUND	1,4,5

Electrical Schematics

