Surface Mount **Bandpass Filter**

50Ω 470 to 520 MHz

The Big Deal

- High rejection (70 dB typical)
- Linear phase (± 9deg typical over Fc ± 30 MHz)
- Miniature shielded case

BPF-C495+



CASE STYLE: HU1186

Product Overview

The BPF-C495+ is a narrow band pass filter in a metal shielded package (size of 0.87" x 0.80" x .25") fabricated using SMT technology. The BPF-C495+ offers a typical pass band insertion loss of 1.7 dB with sharp roll-off and stopband rejection down to 90 dB typ. In addition, it has repeatable performance across production lots and consistent performance across temperature.

Key Features

Feature	Advantages
Minimal Phase deviation over attenu- ation range: ± 9 deg typical over Fc ±30MHz.	Can provide low signal distortion for high data rate communication systems.
High rejection, 70dB typical	Achieving 90dB rejection at 1200MHz; the BPF-C495+ provides a versatile anti aliasing solution for high data rate receivers.
Good VSWR, 1.3:1 typical over passband	The BPF-C495+ has very good return loss over the operating bandwidth which enables low ripple interface when cascaded with other devices.
Sharp roll off	Provides good rejection of signals close to the passband, for improved system performance.
Metal SMT shielded case	Reduced interference to, and from surrounding components.

- A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



Notes

Surface Mount **Bandpass Filter**

50Ω 470 to 520 MHz

BPF-C495+



CASE STYLE: HU1186

Features

- · High rejection, 70 dB typical
- Linear phase, up to ±9 deg typical over Fc ±30MHz
- · Good VSWR, 1.3:1 typical in passband
- · Sharp insertion loss roll off
- · Shielded case
- Aqueous washable

Applications

- · Harmonic rejection
- Transmitters / receivers
- TV broadcasting

Electrical Specifications at 25°C							
Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Center Frequency	Fc			495		MHz
Pass Band	Insertion Loss VSWR	F1-F2 F1-F2	470-520 470-520		2.0 1.3	3.0 1.8	dB :1
Stop Band, Lower	Insertion Loss VSWR	DC-F3 DC-F3	DC-410 DC-410	20	27 29		dB :1
Stop Band, Upper	Insertion Loss VSWR	F4-F5 F4-F5	625-2600 625-2600	20	30 27		dB :1
Maximum Deviation from Linear Phase		Fc ±30MHz	465-525		±9	±18	deg

Maximum	Ratings
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	1W max.

Permanent damage may occur if any of these limits are exceeded

Functional Schematic



Typical Frequency Response





VSWR Frequency (MHz) Insertion Loss Frequency (MHz) **Group Delay** (dB) (:1) (nsec) 211.87 0.5 87.14 465.0 8.60 370.0 48.91 74.88 466.0 7.39 3.46 28 64 470.0 410.0 28 18 430.0 14.83 11.27 472.0 1.95 440.0 450.0 8.14 4.95 474.0 476.0 0.70 3 85 2.08 -0.34 460.0 2.45 478.0 -1.18 1.34 470.0 2.06 1.25 480.0 -1.85 480.0 1.90 1.30 484.0 -2.75 495.0 1.79 1.26 490.0 -3.21 510.0 1.76 1.15 495.0 -2.93 1.78 500.0 -2.22 520.0 1.13 550.0 3.17 1.90 503.0 -1.63 560.0 6.57 2.63 504.0 -1.41 506.0 -0.94 575.0 11.67 8.09 600.0 21.88 17.81 510.0 0.10 625.0 29.80 27.07 515.0 1.47 57.93 2.28 700.0 46.47 518.0 1200.0 90.71 145.46 520.0 2.81 2600.0 52.36 51.57 525.0 3.99

Typical Performance Data at 25°C







Notes

300 600

0

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/WCLStore/terms.jsp

Mini-Circuits

470 480

900 1200 1500 1800 2100 2400 2700 FREQUENCY (MHz)

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A M160513 BPF-C495+ EDB-9350AUE1 RAV/URJ/NY 161230 Page 2 of 3

Bandpass Filter



Pad Connections

INPUT	2
OUTPUT	9
NOT CONNECTED	6,13
GROUND	1,3,4,5,7,8,10,11,12,14

Demo Board MCL P/N: TB-500+ Suggested PCB Layout (PL-294)



Outline Drawing



Outline Dimensions (inch)

н	G	F	E	D	С	В	А
.040	.060		.097	.100	.25	.800	.870
1.02	1.52		2.46	2.54	6.35	20.32	22.10
W		Р	N	М	L	K	J
w grams		P 	N .060	M .060	L 	K .910	J .105
w grams 2.85		P 	N .060 1.52	M .060 1.52	L 	K .910 23.11	J .105 2.67

Notes

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the refits and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp

