Surface Mount **Bandpass Filter**

BPF-C550+

 50Ω 100 to 1000 MHz



Generic photo used for illustration purposes only CASE STYLE: HU1186

The Big Deal

- Sharp roll-off
- Ultra wide bandwidth
- Good VSWR
- Miniature shielded package

Product Overview

The BPF-C550+ is an ultra wide band filter in a small shielded package (size of 0.87" x 0.80" x 0.25") fabricated using SMT technology. This filter offers sharp roll-off and good rejection for use in receiver front end applications.

Key Features

Feature	Advantages
Sharp roll-off	BPF-C550+ attenuates spurious signals and rejects harmonics for wide band of frequency.
Good VSWR over ultra wide bandwidth	This filter maintains typical 1.5 VSWR over ultra wide passband frequency range making this filter easier to integrate into receiver and transmitter RF chains with less concerns for in band frequency ripple.
Small size, 0.87" x 0.80" x 0.25"	The unique surface mount package enables the BPF-C550+ to be used in compact design.

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warnanty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Bandpass Filter

 50Ω 100 to 1000 MHz

BPF-C550+



Generic photo used for illustration purposes only

CASE STYLE: HU1186

Features

- · Sharp roll-off
- Ultra wide bandwidth
- Good VSWR
- · Miniature shielded package

Applications

- Test and measurement
- · Receiver front end applications
- · Civil aircraft communication radio

- · Cellular network


Parar	Parameter		Frequency (MHz)	Min.	Тур.	Max.	Unit
	Center Frequency	_	_	_	550	_	MHz
Pass Band	Insertion Loss	F1-F2	100-1000	_	1.1	2.2	dB
	VSWR	F1-F2	100-1000	_	1.5	2.1	:1
Cton Bond Lawer	Insertion Loss	DC-F3	DC-80	35	46	_	dB
Stop Band, Lower	Stop Band, Lower VSWR		DC-80	_	20	_	:1
Stop Band, Upper	Insertion Loss	F4-F5	1200-2000	30	39	_	dB
Stop Ballu, Opper	VSWR	F4-F5	1200-2000	_	20	_	:1

Electrical Specifications at 25°C


Maximum Ratings				
Operating Temperature	-40°C to 85°C			
Storage Temperature	-55°C to 100°C			
RF Power Input	1W			

Permanent damage may occur if any of these limits are exceeded.

Functional Schematic




Typical Frequency Response





+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1.0	104.03	203.05	100	25.74
50.0	68.47	120.93	150	4.59
80.0	54.18	21.35	200	3.29
83.5	30.52	12.73	250	2.22
85.5	20.18	8.56	300	1.74
88.0	10.30	4.68	350	1.48
92.0	3.15	2.19	400	1.33
100.0	1.11	1.14	450	1.24
550.0	0.42	1.29	500	1.19
1000.0	0.85	1.17	550	1.18
1090.0	3.01	1.61	600	1.18
1112.0	9.84	5.59	650	1.21
1120.0	13.67	7.94	700	1.26
1133.0	20.55	11.45	750	1.32
1149.0	30.36	14.60	800	1.40
1200.0	46.91	20.01	850	1.52
1350.0	44.37	25.02	900	1.74
1500.0	65.83	25.38	950	1.96
1800.0	43.14	25.65	975	2.35
2000.0	42.26	25.13	1000	2.71









Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.


B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp


Pad Connections

INPUT	2
OUTPUT	9
GROUND	1,3,4,5,7,8,10,11,12,14
NOT CONNECTED	6.13


Demo Board MCL P/N: TB-500+ Suggested PCB Layout (PL-294)




- 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B, DIRELECTRIC THICKNESS: .030" ± .002"; COFPER: 1/2 0Z ON EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED. BOTTOM SIDE OF THE FCB IS CONTINUOUS GROUND PLANE.



Outline Drawing



PCB Land Pattern



Suggested Layout, Tolerance to be within ±.002

Outline Dimensions (inch)

Н	G	F	E	D	С	В	Α
.040	.060		.097	.100	.25	.800	.870
1.02	1.52		2.46	2.54	6.35	20.32	22.10
wt		Р	N	М		V	
Wι		Р	IN	IVI	L	K	J
grams			.060	.060		.910	.105
2.85			1.52	1.52		23.11	2.67

Note: Please refer to case style drawing for details

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp

