Surface Mount

Bandpass Filter

 50Ω 470 to 705 MHz

BPF-C587+



Generic photo used for illustration purposes only CASE STYLE: HU1186

The Big Deal

- Sharp roll-off
- Flatness 1.0 dB typical over the passband
- Wide bandwidth
- Good VSWR
- Miniature shielded package

Product Overview

The BPF-C587+ is a wide band filter in a small shielded package (size of 0.87" x 0.80" x 0.25") fabricated using SMT technology. This filter offers sharp roll-off and rejection of 25 dB Typ. for use in HDTV broadcasting.

Key Features

Feature	Advantages
Sharp roll-off	Provides good rejection of signals close to passband for improved systems performance.
Good VSWR	This filter maintains typical VSWR over passband frequency range making this filter easier to integrate into receiver and transmitter RF chains with less concerns for in band frequency ripple.
Flatness 1.0 dB typical	Better flatness over the full HDTV broadcasting band (420-705 MHz) making this ideal for use in applications where flatness and repeatability are critical performance requirements.
Metal SMT Shielded case.	Reduced interference to, and from surrounding components.

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Bandpass Filter

 50Ω 470 to 705 MHz



Generic photo used for illustration purposes only CASE STYLE: HU1186


Features

- · Sharp roll-off
- · Wide bandwidth
- Good VSWR
- · Miniature shielded package


Applications

- · Harmonic rejection
- TV Broadcasting / HDTV
- Transmitters / Receivers

Functional Schematic



Typical Frequency Response



+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C


•							
Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Center Frequency	_	_	_	587	_	MHz
Pass Band	Insertion Loss	F1-F2	470-705	_	2.0	2.5	dB
	Flatness	F1-F2	470-705	_	1.0	1.5	dB
	VSWR	F1-F2	470-705	_	1.7	1.9	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC-400	25	30	_	dB
Stop Ballu, Lower	VSWR	DC-F3	DC-400	_	20	_	:1
Stop Band, Upper Insertion Loss		F4-F5	800-1500	20	25	_	dB
Stop Baild, Opper	VSWR	F4-F5	800-1500	_	20	_	:1


Maximum	Ratings
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	1 W


Permanent damage may occur if any of these limits are exceeded.


Typical Performance Data at 25°C

	• • • • • • • • • • • • • • • • • • • •			
Frequency	Insertion Loss	VSWR	Frequency	Group Delay
(MHz)	(dB)	(:1)	(MHz)	(nsec)
1	102.01	352.40	470	13.22
50	83.87	442.67	480	9.11
200	55.72	190.60	490	7.17
400	33.32	37.80	500	6.03
446	22.17	7.15	510	5.32
448	16.82	5.41	520	4.83
450	12.33	3.84	530	4.45
458	3.43	1.16	540	4.16
470	1.61	1.30	550	3.92
587 705	0.67 0.99	1.30 1.17 1.25	587 600	3.44 3.38
720	1.34	1.54	620	3.34
740	2.99	2.74	640	3.35
760	7.69	5.64	650	3.39
784	19.87	9.56	660	3.46
794	29.43	10.86	670	3.58
800	37.59	11.63	680	3.76
1000	34.39	29.94	690	4.01
1250	30.20	36.43	700	4.34
1500	31.49	32.24	705	4.55









Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.


B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Pad Connections

INPUT	2
OUTPUT	9
GROUND	1,3,4,5,7,8,10,11,12,14
NOT CONNECTED	6,13

Demo Board MCL P/N: TB-500+ Suggested PCB Layout (PL-294)




- 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B, DIRELECTRIC THICKNESS: .030" ± .002"; COFPER: 1/2 0Z ON EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED. BOTTOM SIDE OF THE FCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

Outline Drawing



Outline Dimensions (inch)

Н	G	F	Е	D	С	В	Α
.040	.060		.097	.100	.25	.800	.870
1.02	1.52		2.46	2.54	6.35	20.32	22.10
wt		Р	N	М	L	K	J
grams			.060	.060		.910	.105
2.85			1.52	1.52		23.11	2.67

Note: Please refer to case style drawing for details

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp

