

Frequency Mixer

ADE-ED6315/1

Level 10 (LO Power +10 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CD542

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (f _L to f _U)	640		2220	MHz
	RF (f _L to f _U)	640		2220	MHz
	IF	0.3		1000	MHz
Conversion Loss			6.3		dB
LO-RF Isolation			33		dB
LO-IF Isolation			21		dB

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
LO	3
RF	1
IF	4
GROUND	2, 5, 6