

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.00	90.99	0.01	1.00	107.92
5.00	69.87	0.02	10.00	0.58
10.00	58.72	0.06	50.00	1.24
20.00	52.86	0.26	95.00	6.86
50.00	40.35	0.37	110.00	40.88
95.00	24.79	0.73	112.00	47.63
100.00	7.00	4.37	115.00	40.34
102.00	3.93	9.26	117.00	33.32
110.00	1.61	16.91	119.00	28.67
115.00	1.20	21.70	120.00	27.28
119.00	1.18	17.99	125.00	22.64
122.00	1.20	16.61	130.00	19.91
130.00	1.23	16.72	135.00	18.30
135.00	1.40	27.50	140.00	17.41
140.00	1.44	27.77	147.00	17.15
150.00	3.34	8.43	155.00	18.49
161.00	13.95	1.58	160.00	20.47
170.00	20.06	1.05	161.00	20.98
185.00	25.77	0.80	164.00	23.35
190.00	36.25	0.57	168.00	27.89
210.00	84.15	0.34	170.00	29.16
250.00	63.33	0.31	180.00	15.59
300.00	59.94	0.30	200.00	4.33
400.00	59.16	0.33	300.00	5.44
500.00	58.29	0.36	400.00	1.11
600.00	56.37	0.39	500.00	2.21
700.00	49.73	0.45	600.00	0.28
800.00	32.73	4.03	700.00	0.53
900.00	56.28	0.62	850.00	12.99
1000.00	81.11	0.57	1000.00	50.74