Surface Mount **Band Stop Filter**

50Ω 47 to 68 MHz

The Big Deal

- High rejection, 46 dB typical
- Stopband (47 to 68 MHz)
- Miniature shielded package

BSF-C4768+



CASE STYLE: HU1186

Product Overview

The BSF-C4768+ is stopband filter fabricated using SMT Technology. Covering 47 to 68 MHz stopband, this units offer good rejection. This unit uses a miniature high Q capacitors and wire welded inductors for high reliability. It has repeatable performance across production lots and consistent performance across temperature.

Key Features

Feature Advantages			
High rejection, 46 dB typical	BSF-C4768+ enables the filter to attenuate spurious signals and reject harmonics for broadband of frequencies.		
Shielded package	Shielded package (Size of .087" x 0.80" x 0.25") reduced interface with and from the surrounding components.		
Application	Can be used in broadcast and FM system		

- A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



Notes

Surface Mount **Band Stop Filter**

50Ω 47 to 68 MHz

BSF-C4768+



Min.

-

-

30

CASE STYLE: HU1186

Тур.

0.4

1.3

46

9

0.6

1.3

Max.

1.5

17

1.5

1.7

Unit

dB

:1

dB

:1

dB

:1

Features

- · High rejection, 46 dB typical
- Aqueous washable
- Miniature shielded package

Applications

- FM radio
- · Broadcast system
- · Lab use

RF IN

Maximum Ratings Operating Temperature -40°C to 85°C -55°C to 100°C Storage Temperature **RF** Power Input 250 mW max.

Parameter

Pass Band, Lower

Pass Band, Upper

Stop Band

Insertion Loss

Insertion Loss

VSWR

VSWR

VSWR

Rejection

Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C							
Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)					
1	0.03	1.02					
15	0.12	1.21					
32	0.33	1.20					
36	1.08	1.87					
38	4.22	5.17					
39	7.62	10.02					
40	11.96	17.75					
43	27.82	36.20					
47	58.12	46.96					
56	59.54	8.81					
68	55.41	44.55					
71	41.57	37.77					
75	22.06	23.49					
78	11.92	11.46					
80	6.59	5.52					
81	4.59	3.71					
95	0.58	1.22					
120	0.34	1.23					
600	0.23	1.01					
1200	0.42	1.04					

Electrical Specifications at 25°C

Frequency (MHz)

DC - 32

DC - 32

47 - 68

47 - 68

95-1200

95-1200

F#

DC-F1


DC-F1

F4-F5

F4-F5

F2-F3

F2-F3



Notes

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



M160153 BSF-C4768+ EDU1280 UB.I/NY 161230 Page 2 of 3

=


1200

85

Functional Schematic

RF OUT

Typical Frequency Response



+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


REV A




Pin Connections

INPUT	2
OUTPUT	13
NOT CONNECTED	6,9
GROUND	1,3,4,5,7,8,10,11,12,14

Demo Board MCL P/N: TB-378 Suggested PCB Layout (PL-347)



Outline Drawing



Outline Dimensions (inch)

А	В	С	D	E	F	G	н
.870	.800	.25	.100	.097		.060	.040
22.10	20.32	6.35	2.54	2.46		1.52	1.02
J	к	L	м	Ν	Р		wt
J .105	К .910	L 	M .060	N .060	P 		wt grams

Notes

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the refits and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

