

## Frequency Mixer

## ADE-ED7481/1

Level 17 (LO Power +17 dBm)

### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

**CASE STYLE : CD542**

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	5		1100	MHz
	RF (fL to fU)	5		1100	MHz
	IF	10		782	MHz
Conversion Loss	mid band		6.0		dB
	Total Range		6.4		dB
LO-RF Isolation	Low Range		69		dB
	Mid Range		53		dB
	Upper Range		41		dB
LO-IF Isolation	Low Range		54		dB
	Mid Range		42		dB
	Upper Range		29		dB

**Note:** Low Range = [fL to 10fL]      Mid Range = [10fL to fU/2]      Upper Range = [fU/2 to fU]  
mid band = [2fL to fU/2]

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
LO	6
RF	3
IF	2
GROUND	1, 4, 5