# Coaxial **Precision Fixed Attenuator**

## **50**Ω **5W**

#### **Maximum Ratings**

Operating Temperature -55°C to 100°C Storage Temperature -55°C to 100°C\*\* \*\*With mated connectors. Unmated, 85°C max.

2dB

Permanent damage may occur if any of these limits are exceeded

# Outline Drawing "N" FEMALE MALE "N" CONN B±.01 - E A/F D±.05

## Outline Dimensions (inch)

wt	Е	D	В
grams	.812	1.90	.61
49.7	20.62	48.26	15.49

#### **Features**

- DC to 18000 MHz
- precise attenuation
- excellent VSWR, 1.20 typ

DC to 18000 MHz

stainless steel N male and female connectors

#### **Applications**

- matching
- instrumentation
- test set-ups





Generic photo used for illustration purposes only CASE STYLE: DC736 Connectors Model N-Female N-Male BW-N2W5+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

#### **Electrical Specifications**

FREQ. RANGE (MHz)		ACCURACY	DC-4 GHz	VSWR <sup>2</sup> (:1) 4-8 GHz	8-12.4 GHz	MAX. INPUT POWER <sup>3</sup> (W)
f <sub>L</sub> -f <sub>U</sub>	Nom.	ACCURACT	Max.	Max.	Max.	
DC-18000	2	±0.40	1.20	1.25	1.30	5


1. At 25°C, accuracy includes frequency and power variations. Temperature coefficient for attenuation: .0004dB/dB/°C typ. 2. VSWR from 12.4 to 18 GHz, 1.6:1 typ.


3. Average power at 25°C ambient, derate linearly to 2W at 100°C. Peak Power 125W max. 5µsec. pulse width, 100 Hz PRF.


#### **Typical Performance Data**

Frequency (MHz)	Attenuation (dB)	VSWR (:1)
100	1.88	1.01
2000	1.96	1.05
4000	1.96	1.08
6000	2.06	1.13
8000	2.02	1.04
10000	2.10	1.17
12000	2.06	1.15
14000	2.13	1.05
16000	2.19	1.15
18000	2.13	1.25









A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement ins C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Durcharase of this use

Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

# Mini-Circuits

REV. D M151107 EA-8722 BW-N2W5+ 110706 Page 1 of 1