Precision Fixed Attenuator

BW-N30W20+

 50Ω

20W

30dB

DC to 18 GHz

Maximum Ratings

Operating Temperature	-55°C to 100°C**
Storage Temperature	-55°C to 100°C

**85°C with output into open or short.
Permanent damage may occur if any of these limits are exceeded

Features

• DC to 18000 MHz

Applications

 instrumentation • test set-ups

matching

- precise attenuation
- excellent VSWR, 1.30 typ

· high power measurements

• stainless steel N male and female connectors

Generic photo used for illustration purposes only CASE STYLE: DC1645


Connectors Model

N-Female N-Male BW-N30W20+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing



Outline Dimensions (inch)


wt	E	D	С	В	Α
grams		3.04		1.50	
86.0		77.22		38.10	

Electrical Specifications at 25°C

Parameter	Condition (GHz)	Min.	Тур.	Max.	Unit
Frequency Range		DC	_	18	GHz
Attenuation	DC - 18	_	30	_	
	DC- 12.4	29.0	_	31.0	dB
	12.4 - 18	28.5	_	31.5	
	DC - 6	_	_	1.30	
VSWR	6 - 12.4	_	_	1.3	:1
	12.4 - 18	_	_	1.4	
Input Power ¹		_	_	20	W


1. Max. power at 25°C ambient, derate linearly to 4W at 100°C. Peak power 500W max. 5µsec. pulse with, 100Hz PRF.


Electrical Schematic



Typical Performance Data

Frequency (GHz)	Attenuation (dB)	VSWR (:1)
0.01	30.05	1.01
2.0	30.23	1.05
4.0	30.26	1.10
6.0	30.19	1.04
8.0	30.13	1.11
10.0	30.06	1.08
12.4	30.00	1.11
14.0	29.89	1.11
16.0	29.73	1.15
18.0	29.66	1.19





- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp