Precision Fixed Attenuator

BW-S30W5+

 50Ω

5W

30dB

DC to 18000 MHz

Maximum Ratings

Operating Temperature -55°C to 100°C Storage Temperature -55°C to 100°C**

**With mated connectors. Unmated, 85°C max.

Permanent damage may occur if any of these limits are exceeded.

Features

- DC to 18000 MHz
- precise attenuation

Applications

 instrumentation • test set-ups

matching

- excellent VSWR, 1.20 typ.
- stainless steel SMA male and female connectors


Generic photo used for illustration purposes only CASE STYLE: DC737

Connectors Model SMA Female-SMA Male BW-S30W5+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing



Outline Dimensions (inch)

В D Е wt .61 1.20 .312 grams 15.49 30.48 7.92 9.1

Electrical Specifications


FREQ. RANGE (MHz)	ATTENUATION ¹ (dB)		VSWR ² (:1) DC-4 4-8 8-12.4			MAX. INPUT POWER ³ (W)
			GHz	GHz	GHz	
f _L f _U	Nom.	ACCURACY	Max.	Max.	Max.	
DC-18000	30	±0.85	1.20	1.25	1.30	5


- 1. At 25°C, accuracy includes frequency and power variations. Temperature coefficient for attenuation: .0004dB/dB/°C typ.
- 2. VSWR from 12.4 to 18 GHz, 1.6:1 typ.
- 3. Average power at 25°C ambient, derate linearly to 2W at 100°C. Peak Power 125W max. 5µsec pulse width, 100 Hz PRF.


Typical Performance Data

Attenuation (dB)	VSWR (:1)
20.02	1.00
	1.02
	1.02
	1.09
29.89	1.06
29.85	1.04
29.87	1.13
29.74	1.10
29.68	1.11
29.59	1.05
	30.02 30.03 29.96 30.02 29.89 29.85 29.87 29.74 29.68

Electrical Schematic







A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Ferms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Ferms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp