

## Frequency Mixer

## ADE-EDR4970/2

Level 17 (LO Power +17 dBm)

### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

**CASE STYLE : CD636**

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	1380		1785	MHz
	RF (fL to fU)	1380		1785	MHz
	IF	300		350	MHz
Conversion Loss			8.8		dB
LO-RF Isolation		17	25		dB
LO-IF Isolation		21	27		dB

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
LO	6
RF	3
IF	2
GROUND	1, 4, 5