

High Reliability Mixer

ADE-R1LH+

Level 10 (LO Power +10 dBm) 1 to 500 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
IF Current	40mA
Permanent damage may occur if any of these limits are exceeded.	


Pin Connections

LO	6
RF	3
IF	2
GROUND	1,4,5

Outline Drawing




PCB Land Pattern

Suggested Layout,
Tolerance to be within ±0.02

Outline Dimensions (inch)

A	B	C	D	E	F	G
.272	.310	.220	.100	.162	.055	.100
6.91	7.87	5.59	2.54	4.11	1.40	2.54
H	J	K	L			
.030	.026	.065	.300			
0.76	0.66	1.65	7.62			
						wt
						grams
						0.25

Demo Board MCL P/N: TB-03 Suggested PCB Layout (PL-052)



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- hermetically sealed ceramic quad
- low conversion loss, 5.2 dB typ.
- excellent L-R isolation, 60 dB typ. and L-I isolation, 45 dB typ.
- good IP3, 15 dBm typ.
- low profile package
- aqueous washable
- protected by US Patent 6,133,525

Applications

- VHF/UHF receivers



Generic photo used for illustration purposes only

CASE STYLE: CD636

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel
at no extra cost

Reel Size	Devices/Reel
7"	20, 50, 100, 200
13"	500, 1000

Electrical Specifications

FREQUENCY (MHz)		CONVERSION LOSS (dB)				LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)			IP3 at center band (dBm)
LO/RF	IF	Mid-Band m		Total Range Max.	8.2	L	M	U	L	M	U	
		$\bar{X}$	σ			Typ. Min.	Typ. Min.	Typ. Min.	Typ. Min.	Typ. Min.	Typ. Min.	
1-500	DC-500	5.2	0.10	6.5	8.2	70 55	60 45	47 32	65 45	45 28	34 20	15


1 dB COMP.: +5 dBm typ.

L = low range [f_L to $10 f_L$] M = mid range [$10 f_L$ to $f_U/2$] U = upper range [$f_U/2$ to f_U]
m = mid band [$2f_L$ to $f_U/2$]

Typical Performance Data







Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +10dBm	LO +10dBm	LO +10dBm	LO +10dBm	LO +10dBm
1.00	31.00	5.74	67.64	54.38	1.43	2.25
2.80	32.80	5.29	67.42	53.90	1.24	2.25
6.40	36.40	5.07	66.61	53.33	1.19	2.25
8.20	38.20	5.01	65.84	52.86	1.18	2.25
10.00	40.00	4.86	65.97	52.56	1.18	2.25
12.00	42.00	4.98	66.11	52.18	1.18	2.24
37.00	67.00	5.01	63.03	47.76	1.15	2.24
62.00	92.00	5.02	61.12	44.77	1.14	2.22
87.00	117.00	5.05	59.81	42.86	1.12	2.21
112.00	142.00	5.07	58.70	41.66	1.11	2.26
120.00	150.00	5.08	58.36	41.21	1.11	2.27
210.00	180.00	5.16	58.09	40.10	1.08	2.26
250.00	220.00	5.20	55.11	38.90	1.06	2.31
300.00	270.00	5.30	54.56	38.23	1.05	2.34
350.00	320.00	5.47	49.49	36.88	1.03	2.47
400.00	370.00	5.58	45.89	35.18	1.05	2.41
425.00	395.00	5.56	44.38	33.02	1.09	2.43
450.00	420.00	5.61	43.62	30.95	1.11	2.56
475.00	445.00	5.63	43.19	29.44	1.09	2.52
500.00	470.00	5.73	42.63	28.27	1.06	2.53

Electrical Schematic



Performance Charts

ADE-R1LH+



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

