CBP-1307C+

 50Ω 1215 to 1400 MHz

The Big Deal

- Excellent Rejection
- Low passband Insertion Loss
- Miniature shielded package



Generic photo used for illustration purposes only CASE STYLE: MP1766

Product Overview

CBP-1307C+ is a ceramic-coaxial-resonator based bandpass filter in a shielded package fabricated using SMT technology. This filter offers outstanding close in rejection, low insertion loss and high power handling for use in aviation, mobile radio, broadband and fixed wireless.

Key Features

Feature	Advantages
High Selectivity	The CBP-1307C+ filter incorporates High-Q ceramic resonators that enables sharp rejection near passband.
Low Passband VSWR	This filter maintains typical VSWR over a wide passband frequency range making this filter easier to integrate into receiver and transmitter RF chains with less concerns for in band frequency ripple.
Rugged construction	The CBP-1307C+ has been qualified over wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles.

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Bandpass Filter

 50Ω 1215 to 1400 MHz

CBP-1307C+



Generic photo used for illustration purposes only

CASE STYLE: MP1766


Features

- · Low Insertion loss
- High selectivity
- Miniature shielded package


Applications

- Aviation
- Mobile radio
- Broadband
- · Fixed wireless transmitters and receivers

Functional Schematic



Typical Frequency Response



+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C


Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit		
	Center Frequency	_	_	_	1307.5	_	MHz		
Pass Band	Insertion Loss	F1-F2	1215-1400	_	0.6	2	dB		
	VSWR	F1-F2	1215-1400	_	1.2	_	:1		
Stop Band, Lower	Insertion Loss	DC-F3	DC-1000	20	28	_	dB		
	VSWR	DC-F3	DC-1000	_	39	_	:1		
Stop Band, Upper	Insertion Loss	F4-F5	1820-2500	20	28	_	dB		
	VSWR	F4-F5	1820-2500	_	40	_	:1		


Maximum Ratings							
Operating Temperature	-40°C to 85°C						
Storage Temperature	-55°C to 100°C						
RF Power Input	5W						


Permanent damage may occur if any of these limits are exceeded.


Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1.0	59.57	868.59	1215.0	3.34
35.0	84.60	1737.18	1220.0	3.27
175.0	100.86	868.59	1230.0	3.14
425.0	76.91	193.02	1245.0	2.97
860.0	54.95	62.05	1255.0	2.87
1000.0	28.73	46.96	1265.0	2.80
1095.0	10.27	16.56	1270.0	2.77
1120.0	5.66	7.41	1280.0	2.71
1145.0	2.48	3.17	1285.0	2.68
1175.0	1.00	1.60	1295.0	2.64
1215.0	0.63	1.13	1300.0	2.61
1307.0	0.53	1.05	1307.0	2.59
1307.5	0.53	1.05	1307.5	2.59
1400.0	0.54	1.11	1320.0	2.55
1470.0	1.29	2.18	1335.0	2.51
1510.0	3.09	4.41	1345.0	2.49
1560.0	6.99	11.53	1360.0	2.48
1625.0	12.80	27.59	1370.0	2.49
1820.0	28.57	51.10	1385.0	2.50
2500.0	62.73	48.26	1400.0	2.52









Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.


B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Pad Connections


INPUT	1
OUTPUT	10
GROUND	2.3.4.5.6.7.8.9.11.12.13

Demo Board MCL P/N: TB-684+ Suggested PCB Layout (PL-373)




NOTES:

- TRACE WIDTH IS SHOWN FOR OAK (OAK-602) WITH DIELECTRIC THICKNESS
 .022"±.0015". COPPER: 1/2 OZ. EACH SIDE.
 FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Outline Drawing



Outline Dimensions (inch)

A . 750 19.05	. 750 19.05	C . 210 5.33	D .139 3.53	E . 157 3.99	F . 215 5.46	G . 160 4.06	H . 218 5.54	J . 157 3.99	. 100 2.54	. 060 1.52	M .069 1.75	N . 149 3.78
P . 790 20.07	Q . 541 13.74	R . 790 20.07	S . 499 12.67	T .384 9.75	. 203 5.16	.080 2.03	. 069 1.75	.630	. 630 16.00	Z .145 3.68		wt, grams 4.6

Note: Please refer to case style drawing for details

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Firms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

