Surface Mount **Bandpass Filter**

50Ω 1780 to 1980 MHz

CBP-1880E+

The Big Deal

- Low-profile shielded package
- Low passband Insertion Loss
- Excellent Rejection



Product Overview

CBP-1880E+ is a ceramic-coaxial-resonator based bandpass filter in a shielded package (size of 0.638" x 0.434" x 0.105") fabricated using SMT technology. This filter offers outstanding close in rejection, low insertion loss and high power handling for use in broadband, fixed wireless, image rejection and point-to-point radio. In addition, this model uses low profile resonators which gives very good size advantage.

Key Features

| Feature | Advantages |
|---------------------|---|
| High Selectivity | The CBP-1880E+ filter incorporates High-Q ceramic resonators that enables sharp rejection near passband. |
| Low Passband VSWR | This filter maintains typical VSWR over a wide passband frequency range making this filter easier to integrate into receiver and transmitter RF chains with less concerns for in band frequency ripple. |
| Rugged construction | The CBP-1880E+ has been qualified over wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles. |

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. G. The parts covered by this specification document are subject to Mini-Circuits trandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Surface Mount **Bandpass Filter**

50Ω 1780 to 1980 MHz

CBP-1880E+



Generic photo used for illustration purposes only CASE STYLE: LW1611


Features

- Low Insertion loss
- · Minimal Insertion loss variation over operating temperature
- · Low-profile shielded package


Applications

- · Cordless telephony system
- · Public cellular networks, GSM
- · Wireless audio applications
- PCS broadband

Functional Schematic



Typical Frequency Response





Electrical Specifications at 25°C

| Parar | neter | F# | Frequency (MHz) | Min. | Тур. | Max. | Unit |
|------------------|------------------|-------|-----------------|------|------|------|------|
| | Center Frequency | — | — | _ | 1880 | — | MHz |
| Pass Band | Insertion Loss | F1-F2 | 1780-1980 | - | 1.5 | 3 | dB |
| | VSWR | F1-F2 | 2 1780-1980 | | 1.5 | 2.3 | :1 |
| Sten Band Lawer | Insertion Loss | DC-F3 | DC-1550 | 20 | 37 | _ | dB |
| Stop Band, Lower | VSWR | DC-F3 | DC-1550 | _ | 25 | — | :1 |
| Stop Band, Upper | Insertion Loss | F4-F5 | 2150-3300 | 20 | 30 | _ | dB |
| Stop Band, Opper | VSWR | F4-F5 | 2150-3300 | _ | 14 | — | :1 |


| Maximum Ratings | | | | | | | |
|-----------------------|-------------------|--|--|--|--|--|--|
| Operating Temperature | -40°C to 85°C | | | | | | |
| Storage Temperature | -55°C to 100°C | | | | | | |
| RF Power Input* | 6.3W max. at 25°C | | | | | | |


*Derate linearly to 3.1W at 85°C Permanent damage may occur if any of these limits are exceeded.


Typical Performance Data at 25°C

| F | | | | Orean Delevi | |
|--------------------|------------------------|--------------|--------------------|-----------------------|--|
| Frequency (MHz) | Insertion Loss (dB) | VSWR (:1) | Frequency (MHz) | Group Delay (nsec) | |
| 1 | 99.93 | 1737.18 | 1780 | 4.54 | |
| 80 | 100.42 | 1737.18 | 1780 | 4.54 | |
| 500 | 84.52 | 248.17 | 1790 | 4.40 | |
| 1550 | 39.63 | 29.46 | 1800 | 4.28 | |
| 1560 | 37.02 | 28.03 | 1810 | 4.19 | |
| 1600 | 26.31 | 20.22 | 1820 | 4.13 | |
| 1624 | 19.61 | 15.39 | 1840 | 4.03 | |
| 1650 | 12.42 | 9.58 | 1860 | 4.00 | |
| 1660 | 9.89 | 7.44 | 1880 | 4.01 | |
| 1780 | 1.41 | 1.24 | 1887 | 4.01 | |
| 1880 | 1.25 | 1.21 | 1890 | 4.02 | |
| 1980 | 1.48 | 1.27 | 1900 | 4.04 | |
| 2025 | 3.20 | 2.28 | 1910 | 4.07 | |
| 2040 | 5.78 | 4.51 | 1920 | 4.12 | |
| 2070 | 13.16 | 13.39 | 1940 | 4.24 | |
| 2150 | 31.09 | 34.07 | 1960 | 4.44 | |
| 2160 | 33.08 | 36.20 | 1965 | 4.52 | |
| 2180 | 37.17 | 39.49 | 1970 | 4.61 | |
| 2200 | 41.30 | 41.37 | 1975 | 4.72 | |
| 3300 | 55.89 | 43.44 | 1980 | 4.85 | |









Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

∭Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.B M174392 CBP-1880E+ EDU1469/1 URJ 200813 Page 2 of 3


Bandpass Filter

CBP-1880E+

Pad Connections

| INPUT | 1 |
|--------|-----------------------------------|
| OUTPUT | 11 |
| GROUND | 2,3,4,5,6,7,8,9,10,12,13,14,15,16 |

Demo Board MCL P/N: TB-611+ Suggested PCB Layout (PL-338)




NOTES:

- 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .060"±.004". COPPER: 1/2 OZ. EACH SIDE.
- FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED. 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Outline Drawing



| Outline Dimensions (inch) | | | | | | | | | | | |
|-----------------------------|--------------------------|--------------------------|---------------------------|---------------------|--------------------------|---------------------------|--------------------------|--------------------------|--------------------------|--------------------|---------------------------|
| A .434 11.02 | B .638 16.21 | C .120 3.05 | D . 060 1.52 | E .030 0.76 | F .100 2.54 | G . 119 3.02 | H .095 2.41 | J .129 3.28 | K .110 2.79 | L .678 17.22 | M .474 12.04 |
| N .109 2.77 | P .090 2.29 | Q .085 2.16 | | wt, grams 0.8 | | | | | | | |

Note: Please refer to case style drawing for details.

Notes A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Min-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectived, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and meredies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits