

Engineering Development Model

Power Splitter/Combiner

2 Way-90°

ADPQ-ED12602/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CD637

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		100		160 MHz
Isolation	100 - 160 MHz		24	
Insertion Loss				
Average of Coupled Outputs	100 - 160 MHz		0.20	
above 3.0 dB				
Phase Unbalance	100 - 160 MHz		88.930	
				deg.
Amplitude Unbalance	100 - 160 MHz		0.733	
				dB
VSWR	SUM Port		1.10	
	OUT Ports		1.10	
				(:1)
				(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	1
PORT 1	3
PORT 2	6
GND EXT	2, 5
50Ω TERMINATION	4

Functional Diagram

