

Engineering Development Model

RF Transformer

ADT1-ED8224/1

Impedance Ratio : 1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CD542

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		.15		1200 MHz
Insertion Loss *	3 dB Bandwidth		0.15-1200	MHz
	2 dB Bandwidth		0.20-1000	MHz
	1 dB Bandwidth		0.50-650	MHz

Note:

* Insertion Loss is referenced to mid-band loss, 0.35 dB typ.

MAXIMUM RATINGS	
Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.25W
DC Current	30mW

PIN CONNECTIONS	
PRIMARY DOT	3
PRIMARY	1
SECONDARY DOT	4
SECONDARY	6
NOT USED	2,5

