Surface Mount **Directional Coupler** 75Ω 12 dB 5 to 1200 MHz

Features

- very flat couplingvery broadband, multi octave
- temperature stable, LTCC base
- all welded construction
- leads attached for better solderability
- micro miniature coupler
- aqueous washable
- protected by US Patents 6,140,887 & 6,784,521

Applications

- cable tv
- wire-line broadband access

DBTC-12-4-75LX+



Generic photo used for illustration purposes only CASE STYLE: AT1642

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

	Available Tape and Reel at no extra cost
Reel Size	Devices/Reel
7"	20, 50, 100, 200, 500
13"	1000. 2000

Electrical Specifications at 25°C

Parameter	Condition (MHz)	Min.	Тур.	Max.	Unit	
Frequency Range		5		1200	MHz	
Mainline Loss ¹	5-50	_	1.1	1.8		
	50-500	_	1.1	1.4	dB	
	500-1000	_	1.2	1.6		
	1000-1200	_	1.3	1.9		
Nominal Coupling		_	12±05	—	dB	
Coupling Flatness(±)		_	—	±0.6	dB	
Directivity	5-50	17	19	—	dB	
	50-500	15	18	_		
	500-1000	10	17	_		
	1000-1200	8	13	_		
VSWR			1.3		dB	
Input Power	5-50	—	—	0.5	w	
	50-500	-	—	1.0		
	500-1000	-	-	1.0		
	1000-1200		_	1.0		

1. Includes theoretical coupled power loss.

Maximum Ratings

Parameter	Ratings		
Operating Temperature	-40°C to 85°C		
Storage Temperature	-55°C to 100°C		

Permanent damage may occur if any of these limits are exceeded.


Pin Connections

Function	Pin Number		
INPUT	3		
OUTPUT	4		
COUPLED	1		
GROUND	2		
ISOLATE (DO NOT USE)	6		

Product Marking



Electrical Schematic




REV. A M151107 ED-12343A/1 DBTC-12-4-75LX+ DY/CP/AM 190611 Page 1 of 2

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

DBTC-12-4-75LX+





Typical Performance Data

0.76

0.30


1.52

4.67

0.10

0.10

Frequency (MHz)		Coupling (dB)	Directivity (dB)	Return Loss (dB)		
(10112)	In-Out	In-Cpl	(00)	In	Out	Cpl
5.00	1.11	11.92	19.03	18.05	22.21	20.18
50.00	1.04	11.93	19.50	19.49	26.11	21.12
180.00	1.04	11.98	18.67	19.58	26.61	18.80
340.00	1.01	11.99	18.30	20.15	23.62	15.48
500.00	1.05	12.00	16.68	20.32	21.63	12.88
700.00	1.18	12.15	15.13	18.84	19.39	10.88
870.00	1.28	12.24	13.39	19.80	18.65	9.82
1000.00	1.26	12.29	12.40	21.00	18.94	9.27
1100.00	1.32	12.34	11.84	22.53	19.49	8.90
1200.00	1.38	12.41	11.54	24.40	20.24	8.59



Additional Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp