# Surface Mount Directional Coupler

 $50\Omega$ , 13dB coupling, 5 to 1000 MHz

### Features

- very flat couplingvery broadband, multi octave
- temperature stable, LTCC base
- all welded construction
- leads attached for better solderability
- micro miniature coupler
- aqueous washable
- protected by US Patents 6,140,887 & 6,784,521

### **Applications**

- VHF/UHF receivers/transmitters
- cellular

### Electrical Specifications at 25°C

| Parameter                  | Condition (MHz) | Min. | Тур.     | Max. | Unit     |
|----------------------------|-----------------|------|----------|------|----------|
| Frequency Range            |                 | 5    |          | 1000 | MHz      |
|                            | 5-50            |      | 0.7      | 1.3  |          |
| Mainline Loss <sup>1</sup> | 50-500          |      | 0.7      | 1.3  | dB       |
|                            | 500-100         |      | 1.1      | 1.6  |          |
| Nominal Coupling           | 5-1000          |      | 13.0±0.5 |      | dB       |
| Coupling Flatness(±)       | 5-1000          |      |          | ±0.6 | dB       |
|                            | 5-50            | 17   | 21       |      |          |
| Directivity                | 50-500          | 13   | 18       |      | dB       |
|                            | 500-1000        | _    | 13       |      |          |
| VSWR <sup>2</sup>          | 5-1000          |      | 1.2      |      | dB       |
|                            | 5-50            |      |          | 0.5  |          |
| Input Power                | 50-500          |      |          | 1.0  | W        |
|                            | 500-100         |      |          | 1.0  | <u> </u> |

1. Includes theoretical coupled power loss of 0.22 dB at 13 dB coupling.

2. For coupled port VSWR above 500 MHz, 1.4:1 typ.

### **Maximum Ratings**

| Q                     |                |  |  |
|-----------------------|----------------|--|--|
| Parameter             | Ratings        |  |  |
| Operating Temperature | -40°C to 85°C  |  |  |
| Storage Temperature   | -55°C to 100°C |  |  |


Permanent damage may occur if any of these limits are exceeded.

**Product Marking** 

### **Pin Connections**

| Function             | Pin Number |  |  |  |
|----------------------|------------|--|--|--|
| INPUT                | 3          |  |  |  |
| OUTPUT               | 4          |  |  |  |
| COUPLED              | 1          |  |  |  |
| GROUND               | 2          |  |  |  |
| ISOLATE (DO NOT USE) | 6          |  |  |  |

### **Electrical Schematic**



REV. A M151107 ED-8958A DBTC-13-4X+ WZ/CP/AM 190905

# DBTC-13-4X+




Generic photo used for illustration purposes only CASE STYLE: AT1667-1

#### +RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


|           | Available Tape and Reel<br>at no extra cost |
|-----------|---------------------------------------------|
| Reel Size | Devices/Reel                                |
| 7"        | 20, 50, 100, 200                            |
| 13"       | 500, 1000, 2000                             |

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

## **DBTC-13-4X+**




#### PCB Land Pattern



### Outline Dimensions (inch )


| А    | В    | С    | D    | E    | F     |
|------|------|------|------|------|-------|
| .150 | .150 | .150 | .050 | .030 | .025  |
| 3.81 | 3.81 | 3.81 | 1.27 | 0.76 | 0.64  |
| G    | Н    | J    | К    |      | wt    |
| .028 | .050 | .160 | .030 |      | grams |
| 0.71 | 1.27 | 4.06 | 0.76 |      | 0.10  |

Demo Board MCL P/N: TB-278 Suggested PCB Layout (PL-150)



### **Typical Performance Data**

| Frequency<br>(MHz) | Mainline Loss<br>(dB) |        |       | Return Loss<br>(dB) |       |       |
|--------------------|-----------------------|--------|-------|---------------------|-------|-------|
| . ,                | In-Out                | In-Cpl | (dB)  | In                  | Òuť   | Cpl   |
| 5.00               | 0.77                  | 13.08  | 22.34 | 19.78               | 23.72 | 22.27 |
| 10.00              | 0.70                  | 13.00  | 21.94 | 21.65               | 27.70 | 23.92 |
| 50.00              | 0.65                  | 12.95  | 21.49 | 23.18               | 32.43 | 25.26 |
| 100.00             | 0.67                  | 12.98  | 21.06 | 23.12               | 31.88 | 25.46 |
| 300.00             | 0.74                  | 13.04  | 19.82 | 22.41               | 26.20 | 24.99 |
| 500.00             | 0.79                  | 13.05  | 18.10 | 21.80               | 23.68 | 24.06 |
| 600.00             | 0.82                  | 13.03  | 16.98 | 21.37               | 22.90 | 23.20 |
| 800.00             | 0.89                  | 13.01  | 15.16 | 21.11               | 22.22 | 21.19 |
| 900.00             | 0.93                  | 12.99  | 14.48 | 21.34               | 22.35 | 20.16 |
| 1000.00            | 0.98                  | 12.97  | 13.82 | 21.62               | 22.42 | 19.03 |



### **Additional Notes**

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

