

RF Transformer

ADT1.5-ED12126B/4

Impedance Ratio : 1.5

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CD542

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency		3		1200	MHz
Insertion Loss *	3 dB Bandwidth		3 - 1200		MHz
	2 dB Bandwidth		3 - 1200		MHz
	1 dB Bandwidth		4 - 1050		MHz

Notes:

* Insertion Loss is referenced to mid-band loss, 1.11dB typ.

MAXIMUM RATINGS	
Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.25 W
DC Current	30 mA

Configuration :

