Surface Mount Directional Coupler

DBTC-13-5-75L+

13dB coupling, 75Ω . 5 to 1500 MHz

Features

- very flat coupling
- · very broadband, multi octave
- temperature stable, LTCC base
- all welded construction
- · leads attached for better solderability
- · micro miniature coupler
- aqueous washable
- protected by US Patents 6,140,887 & 6,784,521

Applications

- VHF/UHF receivers/transmitters
- cellular
- catv



Generic photo used for illustration purposes only CASE STYLE: AT1030

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

	Available Tape and Reel at no extra cost
Reel Size	Devices/Reel
7"	20, 50, 100, 200, 500
13"	1000, 2000

Electrical Specifications at 25°C

Parameter	Condition (MHz)	Min.	Тур.	Max.	Unit	
Frequency Range		5		1500	MHz	
Mainline Loss¹	5-50		0.9	1.4		
	50-500		1.0	1.5	-ID	
	500-1000		1.1	1.6	dB	
	1000-1500		1.4	2.2		
	5-1000		13.5±0.5		-ID	
Nominal Coupling	1000-1500		13.6±0.5		dB	
	5-1000			±0.6	-ID	
Coupling Flatness(±)	1000-1500			±0.8	dB	
Directivity	5-50	17	21			
	50-500	14	19		-ID	
	500-1000	_	18		dB	
	1000 -1500	_	17			
VSWR ²	5-1000		1.3		dB	
	1000-1500		1.3			
Input Power	5-50 50-500 500-1000 1000-1500			0.5 1.0 1.0 1.0	W	

^{1.} Includes theoretical coupled power loss of 0.21 dB at 13 dB coupling.

Maximum Ratings


Parameter	Ratings			
Operating Temperature	-40°C to 85°C			
Storage Temperature	-55°C to 100°C			

Permanent damage may occur if any of these limits are exceeded.

Pin Connections


Function	Pin Number						
INPUT	3						
OUTPUT	4						
COUPLED	1						
GROUND	2						
ISOLATE (DO NOT USE)	6						

Electrical Schematic




^{2.} For coupled port VSWR above 500 MHz, 1.6:1 typ.

Outline Drawing




PCB Land Pattern



Outline Dimensions (inch)

wt	L	K	J	Н	G	F	Е	D	С	В	Α
grams	.004	.030	.184	.060	.012	.025	.037	.050	.155	.150	.166
0.10	0.10	0.76	4.67	1.52	0.30	0.64	0.94	1.27	3.94	3.81	4.22

Demo Board MCL P/N: TB-279 Suggested PCB Layout (PL-151)



NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.030" ± 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC


DENOTES PCB COPPER LAYOUT WITH SMOBO (SOLDER MASK OVER BARE COPPER)


(SOLDER MASK O


DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB)	Coupling (dB)	Directivity (dB)	Return Loss (dB)			
,	In-Oút	In-Cpl	, ,	In	Ouť	Cpl	
5.00	0.83	13.09	21.69	20.33	25.83	21.73	
10.00	0.80	13.06	21.61	21.17	28.18	22.73	
30.00	0.80	13.06	21.61	21.55	29.45	23.06	
50.00	0.81	13.07	21.48	21.61	29.48	22.74	
70.00	0.83	13.09	21.51	21.69	29.33	22.26	
100.00	0.85	13.11	21.42	21.72	28.86	21.33	
500.00	0.91	13.23	20.04	17.98	19.17	12.15	
700.00	0.94	13.26	19.95	16.94	17.35	10.31	
1000.00	1.02	13.29	21.53	16.89	16.41	8.68	
1500.00	1.52	13.90	17.38	18.50	16.87	7.37	







Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp