# Surface Mount Directional Coupler

75 $\Omega$ , 20dB coupling, 5 to 1250 MHz

# Features

- very flat couplingvery broadband, multi octave
- temperature stable, LTCC base
- all welded construction
- leads attached for better solderability
- micro miniature coupler
- aqueous washable
- protected by US Patents 6,140,887 & 6,784,521

### **Applications**

CATV

# DBTC-20-4-75X+



Generic photo used for illustration purposes only CASE STYLE: AT1667-1

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

|           | Available Tape and Reel<br>at no extra cost |
|-----------|---|
| Reel Size | Devices/Reel                                |
| 7"        | 20, 50, 100, 200                            |
| 13"       | 500, 1000, 2000                             |

#### Electrical Specifications at 25°C

| Parameter                  | Condition (MHz)            | Min. | Тур.      | Max.              | Unit  |  |
|----------------------------|----------------------------|------|-----------|-------------------|-------|--|
| Frequency Range            |                            | 5    |           | 1250              | MHz   |  |
|                            | 5-50                       |      | 0.4       | 0.7               |       |  |
| Mainline Loss <sup>1</sup> | 50-500                     |      | 0.6       | 0.9               | dB    |  |
| Mainine Loss               | 500-1000                   |      | 0.8       | 1.2               | uБ    |  |
|                            | 1000-1250                  |      | 1.1       | 1.5               |       |  |
| Nominal Coupling           | 5-1250                     |      | 20.5 ±0.5 |                   | dB    |  |
| Coupling Flatness(±)       | 5-1250                     |      |           | ±0.9              | dB    |  |
|                            | 5-50                       | 16   | 20        |                   |       |  |
| Directivity                | 5-50 16                    | 13   | 19        |                   | dB    |  |
| Directivity                | 500-1000                   | 7    | 11        |                   | UD UD |  |
|                            | 1000-1250                  | 6    | 9         |                   |       |  |
| VSWR <sup>2</sup>          | 5-1000                     |      | 1.4       |                   | dB    |  |
| Input Power                | 5-50<br>50-500<br>500-1000 |      |           | 0.5<br>1.0<br>1.0 | W     |  |
|                            | 1000-1250                  |      |           | 1.0               |       |  |

1. Includes theoretical coupled power loss of 0.04 dB at 20 dB coupling.

2. For coupled port VSWR above 500 MHz, 1.6:1 typ.

# **Maximum Ratings**

| Parameter             | Ratings        |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85°C  |
| Storage Temperature   | -55°C to 100°C |

Permanent damage may occur if any of these limits are exceeded.


# **Product Marking**



# **Pin Connections**

| Function             | Pin Number |  |  |
|----------------------|------------|--|--|
| INPUT                | 3          |  |  |
| OUTPUT               | 4          |  |  |
| COUPLED              | 1          |  |  |
| GROUND               | 2          |  |  |
| ISOLATE (DO NOT USE) | 6          |  |  |

# **Electrical Schematic**




ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) THAT ROUTES DC FROM RF PORTS TO GROUND. REV. A M151107 ED-10793A/1 DBTC-20-4LX+ WP/CP/AM 190827 Page 1 of 2




# DBTC-20-4-75X+

Demo Board MCL P/N: TB-279 Suggested PCB Layout (PL-151)



# **Outline Drawing**



Suggested Layout, Tolerance to be within±.002

**PCB Land Pattern** 


-D TYP

# Outline Dimensions (inch )

| F     | E    | D    | C    | B    | A    |
|-------|------|------|------|------|------|
| .025  | .030 | .050 | .150 | .150 | .150 |
| 0.64  | 0.76 | 1.27 | 3.81 | 3.81 | 3.81 |
| wt    |      | K    | J    | H    | G    |
| grams |      | .030 | .160 | .050 | .028 |
| 0.10  |      | 0.76 | 4.06 | 1.27 | 0.71 |

## **Typical Performance Data**

| Frequency Ma<br>(MHz) | Mainline Loss<br>(dB) | Coupling<br>(dB) | Directivity<br>(dB) | Return Loss<br>(dB) |       |       |
|-----------------------|-----------------------|------------------|---------------------|---------------------|-------|-------|
|                       | In-Oút                | In-Cpl           |                     |                     | Òuť   | Cpl   |
| 5.00                  | 0.44                  | 20.47            | 19.75               | 25.31               | 27.17 | 23.11 |
| 10.00                 | 0.41                  | 20.40            | 20.84               | 27.21               | 29.99 | 24.93 |
| 100.00                | 0.46                  | 20.44            | 21.31               | 25.84               | 28.18 | 21.27 |
| 400.00                | 0.61                  | 20.30            | 17.52               | 17.30               | 17.77 | 11.54 |
| 600.00                | 0.74                  | 19.99            | 14.13               | 15.36               | 15.44 | 8.94  |
| 800.00                | 0.85                  | 19.98            | 11.96               | 14.44               | 14.31 | 7.43  |
| 1000.00               | 0.98                  | 20.07            | 10.26               | 13.93               | 13.80 | 6.5   |
| 1050.00               | 1.01                  | 20.13            | 10.01               | 13.85               | 13.76 | 6.23  |
| 1100.00               | 1.06                  | 20.21            | 9.66                | 13.53               | 13.35 | 6.08  |
| 1250.00               | 1.18                  | 20.53            | 8.81                | 13.22               | 12.20 | 5.5   |



#### **Additional Notes**

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

