Surface Mount Directional Coupler

DBTC-9-4L+

50 Ω , 9dB coupling, 5 to 1000 MHz

Features

- · very flat coupling
- · very broadband, multi octave
- temperature stable, LTCC base
- all welded construction
- · leads attached for better solderability
- micro miniature coupler
- aqueous washable
- protected by US Patents 6,140,887 & 6,784,521

Applications

- VHF/UHF receivers/transmitters
- cellular



Generic photo used for illustration purposes only
CASE STYLE: AT1030

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Electrical Specifications at 25°C

Parameter	Condition (MHz)	Min.	Тур.	Max.	Unit
Frequency Range		5		1000	MHz
	5-50		1.2	2.0	
Mainline Loss	50-500		1.2	1.8	dB
	500-1000		1.5	2.0	
Nominal Coupling	5-1000		9.0±0.5		dB
Coupling Flatness(±)	5-1000			±0.5	dB
	5-50	17	21		
Directivity	50-500	13	18		dB
	500-1000	_	15		
VSWR	5-1000		1.2		dB
	5-50			0.5	
Input Power	50-500			1.0	W
	500-1000			1.0	

^{1.} Includes theoretical coupled power loss of 0.58 dB at 9 dB coupling

Maximum Ratings


Parameter	Ratings		
Operating Temperature	-40°C to 85°C		
Storage Temperature	-55°C to 100°C		

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

Function	Pin Number			
INPUT	3			
OUTPUT	4			
COUPLED	1			
GROUND	2			
ISOLATE (DO NOT USE)	6			

Electrical Schematic




ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL
COUPLER WITH INTERNAL TRANSFORMER(S) THAT
BOUTTES DO EROUS BE ROPES TO GROUND




^{2.} For coupled port VSWR above 500 MHz, 1.6:1 typ.

DBTC-9-4L+


Outline Drawing





Outline Dimensions (inch)

.166 .150 .050 .037 .025 .012 .060 .184 .030 .004 grams 1.27 0.94 0.64 0.30 1.52 4.67




NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.020" ± 0.0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED. 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.


DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)


DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB)	Coupling (dB)	Directivity (dB)	Return Loss (dB)		
(In-Out	In-Cpl	(/	In	Out	Cpl
5.00	1.18	8.93	21.62	17.90	24.67	18.40
10.00	1.10	8.89	21.70	19.15	29.04	19.50
50.00	1.07	8.87	21.50	20.07	32.70	20.22
100.00	1.09	8.90	20.99	20.12	31.81	20.27
300.00	1.16	8.93	19.47	20.49	30.43	18.93
500.00	1.20	8.90	17.60	21.02	30.62	16.66
600.00	1.23	8.88	16.50	20.89	30.39	15.36
800.00	1.31	8.86	14.74	20.45	30.31	12.91
900.00	1.37	8.85	14.07	20.06	29.26	11.86
1000.00	1.43	8.86	13.44	19.34	27.16	10.86







Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp