

Directional Coupler

DBTC-ED10488/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.

At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : AT790

ELECTRICAL SPECIFICATIONS 75Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency		0.5		1150	MHz
Coupling	Nominal		7.0 ± 1.0		dB
	Flatness		± 1.0		dB
Mainline Loss **	0.5-5 MHz		3.20		dB
	5-575 MHz		2.20		dB
	575-1150 MHz		2.30		dB
Directivity	0.5-5 MHz		13		dB
	5-575 MHz		15		dB
	575-1150 MHz		13		dB
VSWR	0.5-1150 MHz		1.4		(:1)
RF Power Input	0.5-1150 MHz			0.5	W


Note: ** Mainline loss includes theoretical coupled power loss of 0.967 dB at 7 dB coupling.

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
INPUT	3
OUTPUT	4
COUPLED FORWARD	1
GROUND	2
NOT USED***	5, 6

***Pin 5 & 6 must be isolated

Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) THAT ROUTES DC FROM RF PORTS TO GROUND.