

RF Transformer

ADT4-ED7964/1

Impedance Ratio : 4

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CD637

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	0.03		338	MHz
Insertion Loss *				
3 dB Bandwidth		0.03 - 338		MHz
2 dB Bandwidth		0.038 - 302		MHz
1 dB Bandwidth		0.07 - 242		MHz

Note:

* Insertion Loss is referenced to mid-band loss, 0.22dB typ.

MAXIMUM RATINGS	
Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.25 W
DC Current	30 mA

PIN CONNECTIONS	
PRIMARY DOT	3
PRIMARY	1
SECONDARY DOT	4
SECONDARY	6
NOT USED	2,5

Configuration : C

