

MMIC SURFACE MOUNT

Power Splitter/Combiner

Mini-Circuits

THE BIG DEAL

- Ultra-Wide bandwidth, usable over 1.8 to 28 GHz
- High Power Handling, 2.5W as a splitter
- Excellent amplitude unbalance, 0.1 dB typ.
- Good phase unbalance, 1 to 5° typ.
- High ESD level
- Small size, 4x4 mm
- Aqueous washable
- DC passing



EP2K1+

Generic photo used for illustration purposes only CASE STYLE: DG1847

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

APPLICATIONS

- WIMAX
- ISM
- Instrumentation
- Radar
- WLAN
- Satellite communications
- LTE

PRODUCT OVERVIEW

Mini-Circuits EP2K1+ is a MMIC splitter/combiner designed for wideband operation from 2 to 26.5 GHz. This model provides excellent power ratings in a tiny device package (4x4x1 mm), with up to 2.5 W power handling (as a splitter) and up to 1.2A DC current passing. Manufactured using GaAs IPD technology, it provides a high level of ESD protection and excellent reliability.

KEY FEATURES

Feature	Advantages
Wideband, 2 to 26.5 GHz	One power splitter can be used in many applications, saving component count. Also ideal for wideband applications such as military and instrumentation.
Excellent power handling 2.5W as a splitter at 25°C 1.7W internal dissipation as a combiner at 25°C	In power combiner applications, half the power is dissipated internally. EP2K1+ is designed to handle 1.7W internal dissipation as a combiner allowing reliable operation without excessive temperature rise. Similar splitters implemented as Wilkinson splitters on PCB require big resistors and additional heat sinking. As a splitter, EP2K1+ can handle up to 2.5W in a very small package.
DC Passing up to 1.2A	DC current passing is helpful in applications where both RF & DC need to pass through the DUT, such as antenna mounted hardware.
Small size 4 x 4mm QFN package	Tiny footprint saves space in dense layouts while providing low inductance, repeatable transitions, and excellent thermal contact to the PCB.

REV. B ECO-012024 EP2K1+ RS/CP/PS 220222

Mini-Circuits[®]



MMIC SURFACE MOUNT

Power Splitter/Combiner

Mini-Circuits

ELECTRICAL SPECIFICATIONS¹ AT 25°C

Parameter	Frequency (GHz)	Min.	Тур.	Max.	Unit
Frequency Range		2		26.5	GHz
Insertion Loss ² above 3.0 dB	2 - 5	_	0.8	1.3	dB
	5 - 10	_	1.1	1.6	
	10 - 18	_	1.7	2.5	
	18 - 26.5	_	2.4	3.2	
Isolation	2 - 5	6	14	_	dB
	5 - 10	13	22	-	
	10 - 18	14	20	-	
	18 - 26.5	14	21	-	
Phase Unbalance	2 - 5	-	1.5	4	Degree
	5 - 10	-	2.3	6	
	10 - 18	_	3.7	8	
	18 - 26.5	-	5.4	9	
Amplitude Unbalance	2 - 5	-	0.1	0.3	dB
	5 - 10	_	0.1	0.3	
	10 - 18	-	0.1	0.5	
	18 - 26.5	-	0.3	0.7	
VSWR (Port S)	2 - 5	-	1.5	-	:1
	5 - 10	_	1.4	-	
	10 - 18	-	1.4	-	
	18 - 26.5	-	1.4	-	
VSWR (Port 1-2)	2 - 5	-	1.5	-	:1
	5 - 10	-	1.3	-	
	10 - 18	-	1.4	-	
	18 - 26.5	-	1.5	-	

1. Tested on Mini-Circuits Test Board TB-845+


2. Insertion Loss Values are de-embedded from Test Board Loss; 0.3 dB at 2 GHz, 0.5 dB at 5 GHz, 0.8 dB at 10 GHz and 1.3 dB at 18 GHz & 2 dB at 26.5 GHz

MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-40°C to 85°C
Storage Temperature	-65°C to 150°C
Power Input (as a splitter)	2.5W max. at 25°C. Derate linearly to 1.25W at 85°C
Internal Dissipation	1.7W max. at 25°C. Derate linearly to 1.1W at 85°C
DC Current	1.2A max. at 25°C. Derate linearly to 0.6A at 85°C

Permanent damage may occur if any of these limits are exceeded.

PRODUCT MARKING




Marking may contain other features or characters for internal lot control

PAD CONNECTIONS

Function	Pad Number
SUM PORT	3
PORT 1	14
PORT 2	17
NOT USED, GROUND EXTERNALLY	1, 2, 4-13,15-16, 18-24, Paddle

SIMPLIFIED ELECTRICAL SCHEMATIC





MMIC SURFACE MOUNT

Power Splitter/Combiner

Mini-Circuits

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS CLICK HERE


	Data Table
Performance Data	Swept Graphs
	S-Parameter (S3P Files) Data Set (.zip file)
Case Style	DG1847 Plastic package, exposed paddle; lead finish: Matte Tin
Tape & Reel Standard quantities available on reel	F68 7″ reels with 20, 50, 100, 200, 500, 1000 devices 13″ reels with 2000, 3000, 4000 devices
Suggested Layout for PCB Design	PL-472
Evaluation Board	TB-845+
Environmental Ratings	ENV82

ESD RATING

Human Body Model (HBM): Class 2 (2000 to <4000 V) in accordance with ANSI/ESD STM 5.1 - 2001

Machine Model (MM): Class M3 (200 to <400 V) in accordance with ANSI/ESD STM 5.2 - 1999

MSL TEST FLOW CHART



NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits