

#### MMIC SURFACE MOUNT

### Power Splitter/Combiner EP2RCW+ 2 Way-0° 50Ω DC to 8 GHz

Mini-Circuits

#### **THE BIG DEAL**

- Ultra-Wide bandwidth, DC to 8 GHz
- High Isolation, 21 dB typ. at 4 GHz
- Excellent amplitude unbalance, 0.1 dB typ. to 8 GHz
- Good phase unbalance, 1.0 deg. typ. at 4 GHz
- Small size, 5x5 mm
- Aqueous washable
- Patent pending

#### **APPLICATIONS**

- WIMAX
- ISM
- Instrumentation
- Radar
- WLAN
- Satellite communications

#### **PRODUCT OVERVIEW**

Mini-Circuits' EP2RCW+ is a MMIC 2-way 0° splitter/combiner designed for wideband operation from DC to 8.0 GHz supporting many applications requiring high performance across a wide frequency range including all the LTE bands through WiMax and WiFi, as well as instrumentation and more. This models provides excellent power handling up to 0.6W (as a splitter/combiner) with low insertion loss, good isolation, and low phase and amplitude unbalance in a tiny 5 x 5mm QFN package. Manufactured using GaAs IPD technology, the EP2RCW+ not only provides a repeatable performance, but also a high level of ESD protection.

#### **KEY FEATURES**

Feature	Advantages	
Wideband, DC to 8.0 GHz	One power splitter can be used in all the LTE bands through WiMax and WiFi, saving component count. Also ideal for wideband applications such as military and instrumentation.	
High Isolation, 21 dB typ. at 4 GHz Excellent power handling, • 0.6W as a splitter / combiner	In power combiner applications, half the power is dissipated internally. EP2RCW+ is designed to handle 0.6W internal dissipation as a combiner allowing reliable operation without excessive temperature rise.	
Excellent Amplitude unbalance, 0.1 dB typ. Good phase unbalance, 1.0° typ. at 4 GHz	Ideal for Applications such as WMO & phased array radars	
Tiny size, 5 x 5mm QFN package	Tiny footprint saves space in dense layouts while providing low inductance, repeatable transitions, and excellent thermal contact to the PCB.	



Generic photo used for illustration purposes only CASE STYLE: DG1677-2

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



**MMIC SURFACE MOUNT** 



## Power Splitter/Combiner EP2RCW+

#### Mini-Circuits

#### **ELECTRICAL SPECIFICATIONS<sup>1</sup> AT 25°C**

	Parameter	Frequency (GHz)	Min.	Тур.	Max.	Unit	
Frequency Range			DC		8.0	GHz	
		DC - 0.4	-	5.5	5.8		
	0.4 - 0.7	_	5.5	5.9	dB		
Insertion Loss <sup>2</sup> , above 3.0 dB		0.7 - 7.5	_	4.8			6.1
		7.5 - 8.0	_	4.3			4.9
		DC - 0.4	13	16.7	_		
la alati a a		0.4 - 0.7	15	19.5	_	dB	
Isolation		0.7 - 7.5	17	23.0	_		
		7.5 - 8.0	17	22.0	_		
		DC - 0.4	-	0.04	2		
Dhaaa Ulahalaaaa		0.4 - 0.7	_	0.2	2	Degree	
Phase Unbalance		0.7 - 7.5	_	0.9	9		
		7.5 - 8.0	_	1.7	9		
Amplitude Unbalance		DC - 0.4	_	0.01	0.3		
		0.4 - 0.7	_	0.01	0.3		
		0.7 - 7.5	_	0.02	0.4	dB	
		7.5 - 8.0	_	0.01	0.3		
<u>-</u>		DC - 0.4	_	1.1	_		
		0.4 - 0.7	_	1.1	_		
VSWR (Port S)		0.7 - 7.5	_	1.5	_	:1	
		7.5 - 8.0	_	1.3	_		
VSWR (Port 1-2)		DC - 0.4	_	1.6	_	:1	
		0.4 - 0.7	_	1.8			
		0.7 - 7.5	_	1.7	-		
		7.5 - 8.0	_	1.1			
Power Handling	As a splitter	DC - 8	_	_	0.6	14/	
	As a combiner <sup>3</sup>	DC - 8	_	_	0.6	W	

1. Tested on Mini-Circuits Test Board TB-EP2RCW+

De-embedded from Test Board Loss.
As a combiner of non-coherent signals, max. power per port is 0.3 watt

#### **MAXIMUM RATINGS**


Parameter	Ratings
Operating temperature	-55°C to 105°C
Storage temperature	-65°C to 150°C

Permanent damage may occur if any of these limits are exceeded.

#### **PAD CONNECTIONS**


Function	Pad Number
RF IN	21
RF OUT 1	10
RF OUT 2	31
GROUND	9,11,20,22,30,32 & Paddle
NOT USED GROUND EXTERNALLY	1-8, 12-19, 23-29

#### **PRODUCT MARKING**



Marking may contain other features or characters for internal lot control

#### SIMPLIFIED ELECTRICAL SCHEMATIC



#### **Mini-Circuits** www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com PAGE 2 OF 3



**MMIC SURFACE MOUNT** 

# Power Splitter/Combiner **EP2RCW+**

Mini-Circuits


### ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS CLICK HERE

	Data Table
Performance Data	Swept Graphs
	S-Parameter (S3P Files) Data Set (.zip file)
Case Style	DG1677-2 Plastic package, exposed paddle; lead finish: Matte Tin
Tape & Reel Standard quantities available on reel	F68 7" reels with 20, 50, 100, 200, 500 & 1000 devices
Suggested Layout for PCB Design	PL-647
Evaluation Board	TB-EP2RCW
Environmental Ratings	ENV08T1

#### **ESD RATING**

Human Body Model (HBM): Class 2 (Pass 2000V) in accordance with ANSI/ESD STM 5.1 - 2001

#### **MSL TEST FLOW CHART**



NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp