

Active Mixer

AMCY-ED11506A/1

Level 2 (LO Power + 2 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : BJ293

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fu)	1490		2530	MHz
	RF (fL to fu)	1490		2530	MHz
	IF	10		550	MHz
Conversion Loss	Total Range		7.8		dB
LO-RF Isolation			22		dB
LO-IF Isolation			11		dB
Input IP3			+32		dBm
1 dB Compression			+15		dBm
DC Voltage			5		V
DC Current			80		mA

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to +100°C

PIN CONNECTIONS	
LO	1
RF	5
IF	3
DC	7
GROUND	2,4,6,8