

Active Mixer

AMCY-ED12681

Level 0 (LO Power 0 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



CASE STYLE : BJ293

Please click "Back", and then click "Contact Us" for Applications support.

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (f _L to f _u)	440		2358	MHz
	RF (f _L to f _u)	440		2358	MHz
	IF	100		200	MHz
Conversion Loss	Total Range		7.3		dB
LO-RF Isolation			22		dB
LO-IF Isolation			18		dB
Input IP3			+27		dBm
1 dB Compression			+15		dBm
DC Voltage			5		V
DC Current			70		mA

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to +100°C

PIN CONNECTIONS	
LO	1
RF	5
IF	3
DC	7
GROUND	2,4,6,8