



REPLACEMENT PART REFERENCE GUIDE, DAT-31R5-SN+: AN-70-009


ORIGINAL PART: REPLACEMENT PART:

DAT-31R5-SN+



Replacement Part has been judged by Mini-Circuits Engineering as a suitable replacement to Original Part $_a$

MECHANICAL DIMENSIONS & PCB LAND PATTERN



Notes:

a. Suitability for model replacement within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.



CONCLUSION:

1) FORM-FIT-FUNCTIONAL COMPATIBLE_a: Replacement part is Form Fit compatible. Following is a summary of changes/improvements:

Parameter			DAT-31R5-SN+	DAT-31R5A-SN+	
			(Original Part)	(Replacement Part)	
Frequency (G	iHz)		DC-2.4	DC-4	
VDD(V)			+2.7 to +3.3	+2.3 to +3.6, usable to +5.2V	
Vss(V)			-3.3 min to -2.7 max	-3.6 min to -3.2 max	
Control input High (V)			0.7 Vdd to Vdd	+1.17 to +3.6	
Control input Low (V)			0 to 0.3VDD	-0.3 to +0.6	
Idd (μA)			100 μA max.	100 μA max.	
			During turn-on and		
			transition between		
			attenuation states, device		
			may draw up to 2mA.		
Iss (µA)			100 max	40 max	
Control Current (µA)			1 max	1 max, except, 30μA typ for C0.5, C16,	
				PUP1 and 2μA typ. for LE at +3.6V	
Attenuation	Step	<u>Freq</u>	Spec max	Spec max	
accuracy	<u>(dB)</u>	<u>(GHz)</u>			
	8	1-2.4	0.25	0.5	
		2.4-4	Not Specified	0.8	
	16	1-2.4	0.3	0.7	
		2.4-4	Not Specified	1.45	
VSWR (:1) (1-	VSWR (:1) (1-2.4 GHz)		1.5 max	1.6 Max	
Operating Temperature (°C)			-40 to 85	-40 to 105	
Storage Temperature(°C)			-55 to 100	-65 to 150	
ESD (HBM)			Pass 500V	Pass 1500V	
Max Operating Power			Not Specified	From 10 kHz to 50 MHz per Figure 1 (in	
				Model Data Sheet) and +24 dBm above	
				50 MHz	
Absolute Max input Power			+24	+30	
(dBm)					



Notes:

Notes.

A. Suitability for model replacement within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.




2) TYPICAL PERFORMANCE COMPARISONa:

2) ITPICAL PERFORMANCE COMPARISON _a .						
Parameter	Frequency (GHz)	Original Part DAT-31R5-SN+	Replacement Part DAT-31R5A-SN+			
		Average	Average			
I.Loss(dB)	0.01 to 1	1.42	1.20			
	1 to 2.4	1.77	1.46			
	2.4 to 4	2.99	2.16			
Step Accuracy	0.01 to 1	0.02	0.03			
0.5 dB Step (+/-dB)	1 to 2.4	0.01	0.04			
	2.4 to 4	0.06	0.04			
Step Accuracy	0.01 to 1	0.00	0.03			
1.0 dB Step (dB)	1 to 2.4	0.00	0.04			
	2.4 to 4	0.01	0.04			
Step Accuracy	0.01 to 1	0.02	0.03			
2.0 dB Step (dB)	1 to 2.4	0.06	0.05			
,	2.4 to 4	0.10	0.07			
Step Accuracy	0.01 to 1	0.02	0.03			
4.0 dB Step (dB)	1 to 2.4	0.03	0.07			
	2.4 to 4	0.00	0.10			
Step Accuracy	0.01 to 1	0.08	0.02			
8.0 dB Step (dB)	1 to 2.4	0.08	0.13			
	2.4 to 4	0.10	0.37			
Step Accuracy	0.01 to 1	0.10	0.06			
16 dB Step (dB)	1 to 2.4	0.08	0.23			
	2.4 to 4	0.08	0.43			
Step Accuracy	0.01 to 1	0.28	0.11			
31.5 dB Step (dB)	1 to 2.4	0.88	0.18			
	2.2 to 4	1.86	1.46			
Input R.Loss (dB)	0.01 to 1	17.0	18.2			
	1 to 2.4	19.3	18.5			
	2.2 to 4	18.8	18.2			
Output R.Loss (dB)	0.01 to 1	17.4	18.7			
	1 to 2.4	18.94	18.7			
	2.2 to 4	18.5	17.8			



Notes:
a. Suitability for model replacement within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.

3) PERFORMANCE COMPARISON CURVES_a(TYPICAL):




Note: DAT-31R5+ is same as DAT-31R5-SN+ and DAT-31R5A+is same as DAT-31R5A-SN+

Notes:

a. Suitability for model replacement within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.



3) COMPARISON PERFORMANCE CURVES_a (Continued)





Note: DAT-31R5+ is same as DAT-31R5-SN+ and DAT-31R5A+is same as DAT-31R5A-SN+

Notes:

Notes.

A. Suitability for model replacement within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.