Termination, SMA-F

ANNEF-50+

 50Ω DC to 18 GHz

THE BIG DEAL

- Ultra-wideband, DC to 18 GHz
- Excellent return loss, 23 dB typ. up to 18 GHz
- Input power handling up to 1W



Generic photo used for illustration purposes only

Model No.	ANNEF-50+	
Case Style	LL2642	
Connectors	SMA-Female	

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

APPLICATIONS

- Test and measurement equipment
- Test labs
- Defense and aerospace

PRODUCT OVERVIEW

Mini-Circuits' ANNEF-50+ is a wideband 50Ω termination capable of absorbing signals up to 1W from DC to 18 GHz. It provides excellent return loss across its entire operating frequency range, effectively dissipating signal power with minimal reflections. This model has a SMA-female connector. The unit features rugged construction for a long life of use and comes in a gold plated brass body with a gold plated beryllium copper center contact. It only measures $0.56''(1) \times 0.36''$ (dia.).

KEY FEATURES

Feature	Advantages
Wideband, DC to 18 GHz	Extremely wide frequency range provides application flexibility and makes this model ideal for broadband and multi-band use.
Good return loss: • 23 dB up to 18 GHz	Good return loss minimizes signal reflections across multiple-decade frequency range.
Power handling up to 1W	ANNEF-50+ meets a wide range of system power requirements in a small device size.
Wide operating temperature range, -55 to +100° C	Withstands tough operating conditions and is suitable for use near high power componentry where heat rise is common.

REV. A ECO-012138 ANNEF-50+ MCL NY 220301





COAXIAL

Termination, SMA-F

ANNEF-50+

MAXIMUM RATINGS

Parameter	Ratings
Operating temperature	-55°C to 100°C
Storage temperature	-55°C to 100°C


Permanent damage may occur if any of these limits are exceeded.

ELECTRICAL SPECIFICATIONS AT 25°C

Paramete	Condition (GHz)	Min.	Тур.	Max.	Unit
Frequency Range		DC	_	18	GHz
Impedance			50		Ohms
	DC - 4	30	45	_	
Return Loss	4-8	25	40	_	dB
	8 - 18	20	36	_	
Input Power ¹	DC - 18	_	_	1	W

1. Up to 25°C, derates linearly to 325mW at 100°C.

OUTLINE DRAWING




OUTLINE DIMENSIONS (Inch)

wt	Е	D	С	В	Α
grams		.25	.315	.35	.54
3.35		6.4	8.0	9.0	13.7

TYPICAL PERFORMANCE DATA

Frequency (MHz)	Return Loss (dB)
100	57.80
400	54.91
800	50.37
1000	49.04
2000	46.98
4000	39.04
6000	41.29
8000	43.59
12000	31.63
18000	22.66



NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

