SMA Fixed Attenuator

FW-10+

 50Ω **1W** 10dB

DC to 12000 MHz

Maximum Ratings

Operating Temperature -45°C to 100°C Storage Temperature -55°C to 100°C

Permanent damage may occur if any of these limits are exceeded

Features

- wideband coverage, DC to 12000 MHz
- 1 watt rating
- rugged unibody construction
- · off-the-shelf availability
- very low cost

Applications

- impedance matching
- · signal level adjustment

Generic photo used for illustration purposes only


CASE STYLE: FF704

Connectors Model SMA FW-10+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing



Outline Dimensions (inch)

В D Ε .410 1.43 .312 grams 10 41 36.32 7 92 10.0

Electrical Specifications at 25°C


Parameter	Condition (MHz)	Min.	Тур.	Max.	Unit
Frequency Range		DC	_	12000	MHz
	10	_	10±0.3	_	
	DC - 3000	9.6	10.15	10.7	
Attenuation	3000 - 8000	9.85	10.5	11.25	dB
	8000 - 12000	10.25	10.9	11.6	
	DO 0000		4.05	1.00	
	DC - 3000	_	1.05	1.20	
VSWR	3000 - 8000	_	1.15	1.30	:1
	8000 - 12000		1.30	_	
Input Power	DC - 12000	_	_	1.0	W


1. Flatness = variation over band divided by 2.


Typical Performance Data

Frequency (MHz)	Attenuation (dB)	VSWR (:1)
10.00	10.02	1.01
100.00	10.05	1.01
2000.00	10.21	1.02
3000.00	10.29	1.04
6000.00	10.57	1.08
8000.00	10.78	1.16
10000.00	10.88	1.28
11000.00	10.88	1.27
11500.00	10.88	1.26
12000.00	10.88	1.26
15000.00	10.81	1.15

Electrical Schematic







- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement ins.

 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively: "Standard Terms"): Purchases of this part. Ferrormance and updany authorities and contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp