LTCC Bandpass Filter

1420 to 1470 MHz **50**Ω

The Big Deal

- Small size 3.2mm x 1.6mm
- Pass band (1420-1470 MHz)
- Low Insertion Loss (2.0 dB typical)
- Sharp rejection peaks close to stop band

Product Overview

The BFCN-1445+ LTCC Band Pass Filter is constructed with 12 layers in order to achieve a miniature size and high repeatability of performance. Wrap-around terminations minimize variations in performance due to parasitics. Covering 1445 MHz ±25 MHz, these units offer low insertion loss and good rejection.

Key Features

Feature	Advantages				
Small Size (3.20mm x1.6 mm)	Allows for high layout density of circuit boards, while minimizing affects of parasitics.				
Rejection peaks at harmonic frequencies	Provides good rejection of signals at harmonic frequencies, for improved system perfor- mance.				
Wrap around termination	Provides excellent solderability and easy visual inspection capability.				
LTCC construction	Provides a rugged package that is well suited for tough environments including high humidity and high temperature extremes.				

Notes

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp





CASE STYLE: FV1206



Ceramic **Bandpass Filter**

50Ω 1420 to 1470 MHz


Maximum Ratings

Operating Temperature	-55°C to 100°C			
Storage Temperature	-55°C to 100°C			
RF Power Input*	1.5W max. at 25°C			
*Passband rating, derate linearly to 0.25W at 100°C ambient				
Permanent damage may occur if any of these limits are exceeded.				


Pin Connections

RF IN	1
RF OUT	3
GROUND	2,4

Product Marking: 35



Demo Board MCL P/N: TB-270 Suggested PCB Layout (PL-137)



Features

- Small size
- Temperature stable
- LTCC construction

Applications

- Harmonic Rejection
- Transmitters / Receivers





Generic photo used for illustration purposes only

CASE STYLE: FV1206

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel at no extra cost
 Reel Size
 Devices/Reel


 7"
 20, 50, 100, 200, 500, 1000, 3000

Electrical Specifications^{1,2} at 25°C


Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
Pass Band	Center Frequency	_	_	_	1445	_	MHz
	Insertion Loss	F1-F2	1420-1470	_	_	3.0	dB
	VSWR	F1-F2	1420-1470	-	_	2.5	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC-1140	_	20	_	dB
	VSWR	DC-F3	DC-1140	_	25	_	:1
Stop Band, Upper	Insertion Loss	F4-F5	2600-4900	_	25	_	dB
	VSWR	F4-F5	2600-4900	_	20	_	:1

1. Measured on Mini-Circuits Characterization Test Board TB-270.

2. This filter is not intended for use as a DC Blocking circuit element. In Application where DC voltage is present at either input or output ports, blocking capacitors are required at the corresponding RF port.





Functional Schematic




Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
0.30	65.58	1781.84
300.00	37.88	99.19
700.00	38.27	70.89
1000.00	42.94	49.30
1075.00	39.44	40.47
1180.00	21.37	23.31
1300.00	6.24	3.89
1420.00	2.23	1.65
1470.00	2.03	1.31
2050.00	19.89	47.56
2400.00	26.38	60.68
2600.00	29.89	63.30
2800.00	33.65	62.92
3800.00	37.12	47.50
4900.00	32.50	32.93







Notes

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

REV. D M151107 BFCN-1445+ ED-13635/6 AD/CP/AM 190726 Page 2 of 2

