Ceramic **Bandpass Filter**

1893 to 1920 MHz

50Ω


Features

- Small size (0.126"x0.063"x0.051")
- Temperature stable
- · Hermetically sealed
- LTCC construction


Applications


- Harmonic Rejection
- Transmitters / receivers
- PCS

Specification Definition



-ORF OUT RF INO






Pad Connections Input 1 Output 3

2.4

Ground



Frequency (MHz) Min. Max. Typ. 1900 1893 - 1920 2.6 3.2 1893 - 1920 1.4 DC - 1687 35 _ DC - 1687 30 2153 - 5500 25 2153 - 5500 50

VSWR

VSWR

VSWR

Center Frequency

Insertion Loss

Insertion Loss

Insertion Loss

Parameter

 Measured on Mini-Circuits Characterization Test Board TB-518+.
This filter is not intended for use as a DC Blocking circuit element. In Application where DC voltage is present at either input or output ports, blocking capacitors are required at the corresponding RF port

6000

1920

Maximum Ratings

Pass Band


Stop Band, Lower


Stop Band, Upper

Operating Temperature	-40°C to +85°C
Storage Temperature*	-55°C to +100°C
RF Power Input**	2W at 25°C
12 months	

**Passband rating, derate linearly to 0.5W at 85°C ambient Permanent damage may occur if any of these limits are exceeded.

BFCN-1900+





REV. A M151107 ED-15019/1 BFCN-1900+ WZ/CP/AM 190725 Page 1 of 2

]Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

BFCN-1900+



Generic photo used for illustration purposes only CASE STYLE: FV1206-5

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

> Available Tape and Reel at no extra cost Devices/Reel 20, 50, 100, 200, 500,1000, 3000 Reel Size

> > Unit

MHz

dB

:1

dB

:1

dB

:1

Electrical Specifications^{1,2} at 25°C F#

F1 - F2

F1 - F2

DC - F3

DC - F3

F4 - F5

F4 - F5

Functional Schematic

Bandpass Filter

BFCN-1900+


Fu	Full Band Performance			Pass Band Performance			
Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Insertion Loss (dB)	Group Delay (nsec)		
100.00	66.39	138.63	1893.00	2.68	3.54		
500.00	53.03	102.96	1903.00	2.59	3.47		
1000.00	48.53	94.67	1913.00	2.56	3.41		
1200.00	48.68	92.97	1920.00	2.56	3.37		
1660.00	50.31	45.30					
1687.00	40.78	37.21					
1800.00	6.13	2.56					
1893.00	2.68	1.23					
1920.00	2.56	1.23					
2000.00	6.53	4.20					
2153.00	24.20	43.19					
3500.00	36.36	137.82					
4500.00	33.62	95.34					
5500.00	32.30	90.59					


Pad Connections

Input	1
Output	3
Ground	2,4


Outline Drawing

PCB Land Pattern





Suggested Layout, Tolerance to be within ±.002



Outline Dimensions (^{inch} _{mm})

.126	.063	.051	.026	.075	.012	.182	H .104 2.64	.069
.119	.041	.039	N .013 0.33	.024	.020	.039		wt grams .020

Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com