# LTCC Bandpass Filter

BFCN-2360+

2250 to 2470 MHz  $50\Omega$ 

# **The Big Deal**

- Small size 3.2mm x 1.6mm
- Pass band (2250-2470 MHz)
- Low Insertion Loss (2.0 dB typical)
- Sharp rejection peaks close to stop band



## **Product Overview**

The BFCN-2360+ LTCC Band Pass Filter is constructed with 12 layers in order to achieve a miniature size and high repeatability of performance. Wrap-around terminations minimize variations in performance due to parasitics. Covering 2360 MHz ±110 MHz, these units offer low insertion loss and good rejection.

# **Key Features**

Feature	Advantages				
Small Size (3.20mm x1.6 mm)	Allows for high layout density of circuit boards, while minimizing affects of parasitics.				
Rejection peaks at harmonic frequencies	Provides good rejection of signals at harmonic frequencies, for improved system performance.				
Wrap around termination	Provides excellent solderability and easy visual inspection capability.				
LTCC construction	Provides a rugged package that is well suited for tough environments including high humidity and high temperature extremes.				

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.ninicircuits.com/MCLStore/terms.jsp

# **Bandpass Filter**

#### 2250 to 2470 MHz $50\Omega$

### **Maximum Ratings**

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input*	1.5W max. at 25°C


\*Passband rating, derate linearly to 0.25W at 100°C ambient Permanent damage may occur if any of these limits are exceeded.


#### **Pin Connections**

RF IN	11_
RF OUT	3
GROUND	2,4

#### **Product Marking: 38**

#### **Outline Drawing**






#### Outline Dimensions (inch )

A	B	C	D	E	F	G	
.126	.063	.037	.020	.032	.009	.169	
3.20	1.60	0.94	0.51	0.81	0.23	4.29	
H	.024	K	L	M	N	P	wt
.087		.122	.024	.087	.012	.071	grams
2.21		3.10	0.61	2.21	0.30	1.80	.020

#### Demo Board MCL P/N: TB-270 Suggested PCB Layout (PL-137



COPLANAR WAYEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH THICKNESS .020" ± .0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

### **Features**

- Small size
- Temperature stable
- · Hermetically sealed
- LTCC construction

#### **Applications**

- Harmonic Rejection
- Transmitters / Receivers

# **BFCN-2360+**



Generic photo used for illustration purposes only

CASE STYLE: FV1206

#### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications




Electrical Specifications<sup>1,2</sup> at 25°C


Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Center Frequency	_	_	_	2360	_	MHz
Pass Band	Insertion Loss	F1-F6	2250-2330	_	_	5.5	dB
		F6-F2	2330-2470	_	_	3.0	dB
	VSWR	F1-F2	2250-2470	_	2.5	_	:1
Cton Bond Lawer	Insertion Loss	DC-F3	DC-1700	_	20	_	dB
Stop Band, Lower	VSWR	DC-F3	DC-1700	_	25	_	:1
Cton Bond Unner	Insertion Loss	F4-F5	4300-6200	_	25	_	dB
Stop Band, Upper	VSWR	F4-F5	4300-6200	_	20	_	:1

- 1 Measured on Mini-Circuits Characterization Test Board TB-270
- 2. This filter is not intended for use as a DC Blocking circuit element. In Application where DC voltage is present at either input or output ports, blocking capacitors are required at the corresponding RF port

#### **Typical Frequency Response**





#### **Functional Schematic**




#### Typical Performance Data at 25°C

Insertion Loss (dB)	VSWR (:1)
71.17	2878.39
33.29	96.92
37.99	66.84
37.00	58.44
30.04	36.63
18.85	22.64
1.60	1.16
1.80	1.63
20.68	39.85
23.21	40.82
25.91	41.22
32.27	40.97
35.96	36.32
34.66	34.47
32.93	24.67
	(dB) 71.17 33.29 37.99 37.00 30.04 18.85 1.60 1.80 20.68 23.21 25.91 32.27 35.96 34.66







- OBS

  Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
  Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
  The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp