# Surface Mount Monolithic Amplifier

## DC-7 GHz

#### Features

- Miniature SOT-89 Package
- Frequency range, DC to 7 GHz
- Internally Matched to 50 Ohms
- Output power, 10.5 dBm typ.
- Excellent package for heat dissipation, exposed metal bottom
- Aqueous washable
- Protected by US Patent 6,943,629
- Low additive phase noise, typically -172 dBc/Hz @10 KHz offset


#### Applications


- Cellular
- PCS
- Communication receivers & transmitters
- · Suitable for low phase noise applications

#### **General Description**

Gali<sub>=</sub>39+ (RoHS compliant) is a wideband amplifier offering high dynamic range. It has repeatable performance from lot to lot, and is enclosed in a SOT-89 package. It uses patented Transient Protected Darlington configuration and is fabricated using InGaP HBT technology. Expected MTTF is 4,000 years at 85°C case temperature. Gali=39+ is designed to be rugged for ESD and supply switch-on transients.

#### simplified schematic and pin description





Function	Pin Number	Description	
RF IN	1	RF input pin. This pin requires the use of an external DC blocking capacitor chosen for the frequency of operation.	
RF-OUT and DC-IN	3	RF output and bias pin. DC voltage is present on this pin; therefore a DC blocking capacitor is necessary for proper operation. An RF choke is needed to feed DC bias without loss of RF signal due to the bias connection, as shown in "Recommended Application Circuit".	
GND	2,4	Connections to ground. Use via holes as shown in "Suggested Layout for PCB Design" to reduce ground path inductance for best performance.	

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Nini-Circuit's applicable established test performance criteria and measurement instructions. G. The parts covered by this specification document are subject to Mini-Circuit shandard limited warranty and terms and conditions (collectively, "Standard Terms"), Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



CASE STYLE: DF782

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

**Mini-Circuits** 

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. L ECO-005768 D60-1117.DOC Q0201032 GALI-39+ RS/TD/CP/AM 210201 Page 1 of 4

#### Electrical Specifications at 25°C and 35mA, unless noted

Parameter		Min.	Тур.	Max.	Units
Frequency Range*		DC		7	GHz
Gain	f=0.1 GHz	_	20.8	_	dB
	f=1 GHz	_	21.1	_	
	f=2 GHz	17.7	19.7	_	
	f=3 GHz	_	17.7	_	
	f=4 GHz	_	17.0	_	
	f=5 GHz	_	16.1	_	
	f=7 GHz	_	17.6	_	
	f=10 GHz	_	9.8	_	
Input Return Loss	f= DC to 3 GHz		12.5		dB
	f= 3 to 7 GHz		11		
Output Return Loss	f= DC to 3 GHz		14		dB
	f= 3 to 7 GHz		8.0		
Output Power @ 1 dB compression	f=7 GHz	9.0	10.5	—	dBm
Output IP3	f=2 GHz		22.9		dBm
Noise Figure	f=2 GHz		2.4		dB
Additive Phase Noise	2 GHz, 10 KHz offset		-172		dBc/Hz
Recommended Device Operating Current			35		mA
Device Operating Voltage		3.1	3.5	3.9	V
Device Voltage Variation vs. Temperature at		-2.5		mV/°C	
Device Voltage Variation vs. Current at 25°C		2.9		mV/mA	
Zharmal-Besistanaeri 42-4342-43861requenc	v cut off determined by externa	al coupling capa	citors, 127		°C/W

#### **Absolute Maximum Ratings**

Parameter	Ratings		
Operating Temperature*	-45°C to 85°C		
Storage Temperature	-65°C to 150°C		
Operating Current	55mA		
Input Power	13dBm		

Note: Permanent damage may occur if any of these limits are exceeded.

These ratings are not intended for continuous normal operation. <sup>1</sup>Case is defined as ground leads. <sup>\*</sup>Based on typical case temperature rise 2°C above ambient.


Notes
A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Min-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Min-Circuit's and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedities thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuit's 0000 (714) 001 4500, collectively, and there in the terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and termedicise thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp





#### Product Marking



Markings in addition to model number designation may appear for internal quality control purposes.

#### **Additional Detailed Technical Information**

Additional information is available on our web site. To access this information enter the model number on our web site home page.

#### Performance data, graphs, s-parameter data set (.zip file)

#### Case Style: DF782

Plastic package, exposed paddle, lead finish: Matte-Tin


Tape & Reel: F55 7" reels with 20, 50, 100, 200, 500, 1K devices.

#### Suggested Layout for PCB Design: PL-019

Evaluation Board: TB-409-39+

**Environmental Ratings: ENV08T2** 

#### **Recommended Application Circuit**



Test Board includes case, connectors, and components (in bold) soldered to PCB

R BIAS				
Vcc	"1%" Res. Values (ohms) for Optimum Biasing			
7	107			
8	133			
9	162			
10	191			
11	221			
12	249			
13	280			
14	309			
15	340			
16	365			
17	392			
18	422			
19	453			
20	475			

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are entitled to be excluded and benefits contained in the specification are entitled to be excluded and benefits contained in the specification document are not the specification and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits trandard limited warranty and terms and conditions (collectivity, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp





#### **ESD** Rating

Human Body Model (HBM): Class 1A (250V to < 500V) in accordance with ANSI/ESD STM 5.1 - 2001


Machine Model (MM): Class M1 (< 100V) in accordance with ANSI/ESD STM 5.2 - 1999

#### MSL Rating

Moisture Sensitivity: MSL1 in accordance with IPC/JEDECJ-STD-020C

No.	Test Required	Condition	Standard	Quantity
1	Visual Inspection	Low Power Microscope Magnification 40x	MIP-IN-0003 (MCT spec)	45 units
2	Electrical Test	Room Temperature	SCD (MCL spec)	45 units
3	SAM Analysis	Less than 10% growth in term of delamination	J-Std-020C (Jedec Standard)	45 units
4	Moisture Sensitivity Level 1	Bake at 125°C for 24 hours Soak at 85°C/85%RH for 168 hours Reflow 3 cycles at 260°C peak	J-Std-020C (Jedec Standard)	45 units

#### **MSL Test Flow Chart**



Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and beefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

### Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com