Surface Mount Monolithic Amplifier

DC-4 GHz

Product Features

- InGaP HBT microwave amplifier
- Miniature SOT-89 package
- Internally Matched to 50 Ohms
- Frequency range, DC to 4 GHz
- Output power, 18.2 dBm typ.
- Excellent package for heat dissipation, exposed metal bottom
- · Low thermal resistance for high reliability
- Aqueous washable
- Protected by US Patent 6,943,629
- Low additive phase noise, typically -169 dBc/Hz @10 KHz offset

Typical Applications

- Cellular
- PCS
- Communication receivers & transmitters
- Suitable for low phase noise applications

General Description





CASE STYLE: DF782

+ROHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Gali=6+ (RoHS compliant) is a wideband amplifier offering high dynamic range. It has repeatable performance from lot to lot, and is enclosed in a SOT-89 package. It uses patented Transient Protected Darlington configuration and is fabricated using InGaP HBT technology. Expected MTTF is 2,500 years at 85°C case temperature. Gali=6+ is designed to be rugged for ESD and supply switch-on transients.

simplified schematic and pin description





Function	Pin Number	Description	
RF IN	1	RF input pin. This pin requires the use of an external DC blocking capacitor chosen for the frequency of operation.	
RF-OUT and DC-IN	3	RF output and bias pin. DC voltage is present on this pin; therefore a DC blocking capacitor is necessary for proper operation. An RF choke is needed to feed DC bias without loss of RF signal due to the bias connection, as shown in "Recommended Application Circuit".	
GND	2,4	Connections to ground. Use via holes as shown in "Suggested Layout for PCB Design" to reduce ground path inductance for best performance.	

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Nini-Circuit's applicable established test performance criteria and measurement instructions. G. The parts covered by this specification document are subject to Mini-Circuit shandard limited warranty and terms and conditions (collectively, "Standard Terms"), Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp REV. T ECO-005768 D60129 EE-7974Q GALI-6+ RS/YB/FL/AM 210218 Page 1 of 4



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Electrical Specifications at 25°C and 70mA, unless noted

Parameter		Min.	Тур.	Max.	Units
Frequency Range*		DC		4	GHz
Gain	f=0.1 GHz	_	12.2	_	dB
	f=1 GHz	_	12.2	_	
	f=2 GHz	10	11.8	_	
	f=3 GHz	_	11.3	_	
	f=4 GHz	_	11.4	_	
	f=6 GHz	_	12.3	_	
Input Return Loss	f= DC to 3 GHz		14		dB
	f= 3 to 4 GHz		15.5		
Output Return Loss	f= DC to 3 GHz		11		dB
	f= 3 to 4 GHz		9.5		
Output Power @ 1 dB compression	f=1 GHz	16.5	18.2	_	dBm
Output IP3	f=1 GHz		35.5		dBm
Noise Figure	f=1 GHz		4.5		dB
Additive Phase Noise	2 GHz, 10 KHz offset		-169		dBc/Hz
Recommended Device Operating Current			70		mA
Device Operating Voltage		4.6	5.0	5.6	V
Device Voltage Variation vs. Temperature at 70 mA			-3.0		mV/°C
Device Voltage Variation vs. Current at 25°C			11.8		mV/mA
Thermal Resistance, junction-to-case ¹		93		°C/W	

*Guaranteed specification DC-4 GHz. Low frequency cut off determined by external coupling capacitors.

Absolute Maximum Ratings

Parameter	Ratings	
Operating Temperature*	-45°C to 85°C	
Storage Temperature	-65°C to 150°C	
Operating Current	85mA	
Input Power	20dBm	

Note: Permanent damage may occur if any of these limits are exceeded. These ratings are not intended for continuous normal operation. ¹Case is defined as ground leads.


*Based on typical case temperature rise 5°C above ambient.

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits: website at www.minicircuits.com/MCLStore/terms.jsp





Product Marking



Markings in addition to model number designation may appear for internal quality control purposes.

Additional Detailed Technical Information

Additional information is available on our web site. To access this information enter the model number on our web site home page.

Performance data, graphs, s-parameter data set (.zip file)

Case Style: DF782

Plastic package, exposed paddle, lead finish: Matte-Tin


Tape & Reel: F55 7" reels with 20, 50, 100, 200, 500, 1K devices.

Suggested Layout for PCB Design: PL-019

Evaluation Board: TB-409-6+

Environmental Ratings: ENV08T2

Recommended Application Circuit



Test Board includes case, connectors, and components (in bold) soldered to PCB

R BIAS				
Vcc	"1%" Res. Values (ohms) for Optimum Biasing			
7	30.1			
8	43.2			
9	56.2			
10	69.8			
11	84.5			
12	97.6			
13	113			
14	127			
15	140			
16	154			
17	169			
18	182			
19	196			
20	210			

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are entitled to be excluded and benefits contained in the specification are entitled to be excluded and benefits contained in the specification document are not the specification and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits trandard limited warranty and terms and conditions (collectivity, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com



ESD Rating

Human Body Model (HBM): Class 1B (500v to < 1000v) in accordance with ANSI/ESD STM 5.1 - 2001


Machine Model (MM): Class M1 (< 100v) in accordance with ANSI/ESD STM 5.2 - 1999

MSL Rating

Moisture Sensitivity: MSL1 in accordance with IPC/JEDECJ-STD-020C

No.	Test Required	Condition	Standard	Quantity
1	Visual Inspection	Low Power Microscope Magnification 40x	MIP-IN-0003 (MCT spec)	45 units
2	Electrical Test	Room Temperature	SCD (MCL spec)	45 units
3	SAM Analysis	Less than 10% growth in term of delamination	J-Std-020C (Jedec Standard)	45 units
4	Moisture Sensitivity Level 1	Bake at 125°C for 24 hours Soak at 85°C/85%RH for 168 hours Reflow 3 cycles at 260°C peak	J-Std-020C (Jedec Standard)	45 units

MSL Test Flow Chart



Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and beefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com