## Ceramic **LTCC Bandpass Filter**

50Ω 2570 to 4130 MHz

### The Big Deal

- Small size 3.2mm x 2.5mm
- Wide passband (2570-4130 MHz)
- Low Insertion Loss (1.5 dB typical)
- · Wide stopband rejection up to 8 GHz



**BFCV-3350+** 

Generic photo used for illustration purposes only CASE STYLE: JV1210C

### **Product Overview**

The BFCV-3350+ LTCC Band Pass Filter is constructed with multiple layers in order to achieve a miniature size and high repeatability of performance. Wrap-around terminations minimize variations in performance due to parasitics. These units offer low insertion loss and very good wide band rejection.

## **Key Features**

Feature	Advantages			
Small Size (3.20mm x2.5 mm)	Allows for high layout density of circuit boards, while minimizing effects of parasitics.			
Wrap around termination	Provides excellent solderability and easy visual inspection capability.			
Wide bandwidth	Enables high data rate in communication systems.			
LTCC construction	Provides a rugged package that is well suited for tough environments including high humidity and high temperature extremes.			

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard Terms and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



# Ceramic **Bandpass Filter**

50Ω 2570 to 4130 MHz


#### **Features**

- Small size
- Temperature stable
- · Hermetically sealed
- LTCC construction


#### **Applications**

- · Software defined radio
- WLAN
- · Cellular network
- · Satellite television broadcast
- Aircraft radar altimeters

#### **Functional Schematic**



#### **Typical Frequency Response**



+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

CASE STYLE: JV1210C Electrical Specifications<sup>1,2</sup> at 25°C

Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Center Frequency	_	_	_	3350	-	MHz
Pass Band	Insertion Loss	F3-F6	2570-4130		1.5	_	dB
Pass Dallu	Insertion Loss	F4-F5	2650-4030		1.5	3.5	dB
	VSWR	F3-F6	2570-4130	—	2.3	-	:1
	Insertion Loss	DC-F1	DC-1900	14	17	_	dB
Stop Band, Lower		F2	2065	_	17	_	dB
	VSWR	DC-F1	DC-1900	—	20	_	:1
Stop Band, Upper	Insertion Loss	F7-F8	5140-8000	15	20	_	dB
Stop Ballu, Opper	VSWR	F7-F8	5140-8000		20	-	:1

1. Measured on Mini-Circuits Characterization Test Board TB-946+


2. This filter is not intended for use as a DC Blocking circuit element. In Application where DC voltage is present at either input or output ports, blocking capacitors are required at the corresponding RF port.


Maximum Ratings				
Operating Temperature	-55°C to 100°C			
Storage Temperature	-55°C to 100°C			
RF Power Input*	4 W max @ +25°C			


\*Passband rating, derate linearly to 0.25W at 100°C ambient Permanent damage may occur if any of these limits are exceeded


#### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)	
10	48.70	345.89	2570	0.67	
1900	36.32	14.43	2580	0.65	
1960	29.02	14.17	2600	0.62	
2000	23.59	13.72	2650	0.57	
2040	19.59	12.99	2700	0.52	
2065	17.49	12.34	2750	0.49	
2200	8.96	7.24	2800	0.47	
2340	3.39	2.70	2900	0.45	
2570	1.25	1.42	3000	0.44	
2650	1.30	1.69	3350	0.44	
3350	0.85	1.12	3500	0.42	
4030	1.31	1.50	3600	0.42	
4130	1.46	1.37	3700	0.41	
4280	3.06	2.67	3800	0.42	
4600	13.12	18.05	3900	0.46	
4780	20.31	34.49	3950	0.49	
4960	30.12	50.63	4000	0.53	
5140	44.89	64.88	4030	0.55	
7000	32.29	35.51	4100	0.62	
8000	37.45	72.31	4130	0.66	









Notes
 A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuit's tandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and thereadies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.A ECO-006785 BFCV-3350+ EDU2451\_7 URJ 210319 Page 2 of 3

## **BFCV-3350+**



Generic photo used for illustration purposes only




#### **Pad Connections**

RF IN	1
RF OUT	3
GROUND	2,4

Product Marking: HS

Demo Board MCL P/N: TB-946+ Suggested PCB Layout (PL-502)




#### NOTES:

- TRACE WIDTH & SPACE WIDTH IS SHOWN FOR ROGERS (R04350B) WITH DIELECTRIC THICKNESS .0166"±.0015". COPPER 1/2 OZ. EACH SIDE FOR OTHER MATERIALS TRACE WIDTH & SPACE WIDTH MAY NEED TO BE MODIFIED.
- 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

#### **Outline Drawing**



#### Outline Dimensions ( inch )

Α	В	С	D	Е	F	Wt.
.126	.098	.059	.012	.024	.016	grams
3.2	2.5	1.5	.3	.6	.4	.03

Note: Please refer to case style drawing for details

Notes
 A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document of this part are entitled warranty and terms and conditions (collective), "Standard Terms"), Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

