Bandpass Filter

BFHK-6251+

50Ω 5.35 to 6.7 GHz

THE BIG DEAL

- Ultra-High Stopband Rejection Structure 76 dB typical
- Surface mountable pick and place standard case style
- Standard small 1812 (4.5mm x 3.2mm) case style
- · High quality distributed filter topology
- · Wide rejection band
- Shielded construction preventing filter from de-tuning
- Reduced footprint area by employing LGA (land grid array)
- Suited for very high-volume production
- Protected by US Patents 11,638,370 and 11,744,057



Generic photo used for illustration purposes only

CASE STYLE: NM1812C-3

+RoHS Compliant

The +Suffix identifies RoHS Compliance. ee our website for methodologies and qualification

APPLICATIONS

- Test and Measurement
- Aerospace and Defense Signal Conditioning

PRODUCT OVERVIEW

The BFHK-6251+ LTCC Band Pass Filter achieves a miniature size and high repeatability of performance by utilizing a proprietary LTCC material system and distributed filter topology. The passband loss at 5.35 – 6.7 GHz is as low as 3.2 dB, with typical stopbandrejections at 76 dB up to 15.5 GHz. This model handles up to 1W RF input power, and provides a wide operating temperature range from -55 to +125°C. Utilizing a proprietary LTCC material system and a distributed filter topology, this filter is able to achieve repeatable performance on a lot-to-lot basis.

KEY FEATURES

| Feature | Advantages | |
|----------------------------|--|--|
| Ultra-High Rejection | Typical stopband rejections at 76 dB up to 15.5 GHz | |
| Cost effective | LTCC is scalable technology that is cost effective due to ease of production in high quantities. | |
| Small size (4.5mm x 3.2mm) | Allows for high layout density of circuit boards, while minimizing effects of parasitics. | |
| Surface Mountable | Suitable for very high volume automated assembly process. | |

REV. A ECO-019695 BFHK-6251+ WY/CP/AM 231102



Bandpass Filter

BFHK-6251+

ELECTRICAL SPECIFICATIONS¹ AT 25°C

| Para | meter | F# | Frequency (GHz) | Min. | Тур. | Max. | Units |
|------------------|------------------|-------|-----------------|------|------|------|-------|
| | Center Frequency | _ | _ | _ | 6.1 | _ | GHz |
| Pass Band | Insertion Loss | F1-F2 | 5.35 - 6.7 | _ | 3.2 | 4.5 | dB |
| | Return Loss | F1-F2 | 5.35 - 6.7 | _ | 13.0 | _ | dB |
| Stop Band, Lower | Insertion Loss | DC-F3 | 0.1 - 3.5 | 70 | 80 | _ | dB |
| Stop Band, Upper | Insertion Loss | F4-F5 | 8.6 - 15.5 | 66 | 76 | _ | dB |


^{1.} Measured on Mini-Circuits Test Board TB-BFHK-6251C+ with feedline losses removed by normalization of S12 and S21 traces to measurements of TB thru-line

MAXIMUM RATINGS


| Parameter | Ratings |
|-----------------------|----------------|
| Operating Temperature | -55°C to 125°C |
| Storage Temperature | -55°C to 125°C |
| RF Power Input | 1W max. |

Permanent damage may occur if any of these limits are exceeded

TYPICAL FREQUENCY RESPONSE



FUNCTIONAL SCHEMATIC







CERAMIC Bandpass Filter

BFHK-6251+

EVALUATION BOARD MCL P/N: TB-BFHK-6251C+ SUGGESTED PCB LAYOUT: PL-730






- 1. PCB IS MULTILAYER PCB. SEE STACK-UP DIAGRAM.
- 1. FUE IS MOLITIATER FOR SEE STIAGNOW FOR MEGTRONG R-5775(G), CLOTH STYLE:1080 WITH DIELECTRIC THICKNESS .0051; COPPER: 1/2 OZ.+PLATING. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.

 3. COPPER LAYER 4 OF THE FUE ARE CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER) DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

LAYER 2, B-VIA & PTH




LAYER 3 & PTH -R.018, 2PL. 0//0//0/ 6 0 0 0//0 0 0 0 9000000 0000000 .0254, 2 PL. 0000000 0 0 0 0 0 -.135


PAD CONNECTIONS

| INP | UT | 1 | |
|-----|-----|---|--|
| OUT | PUT | 2 | |
| GRO | UND | 3 | |

PRODUCT MARKING: F479

OUTLINE DRAWING








Weight: .126 grams. Dimensions are in inches [mm]. Tolerances: 2Pl.±.01; 3Pl. ±.005


Bandpass Filter


BFHK-6251+

TYPICAL PERFORMANCE DATA

| Frequency (MHz) | Insertion Loss (dB) | Return Loss (dB) |
|--------------------|------------------------|---------------------|
| 100 | 113.36 | 0.13 |
| 1000 | 102.20 | 0.32 |
| 2000 | 93.89 | 0.30 |
| 3000 | 88.32 | 0.43 |
| 3500 | 83.07 | 0.54 |
| 5350 | 2.33 | 24.43 |
| 6700 | 3.11 | 30.02 |
| 7500 | 37.75 | 2.13 |
| 8500 | 80.78 | 1.12 |
| 9500 | 77.42 | 1.06 |
| 10500 | 76.29 | 1.31 |
| 11000 | 76.66 | 1.35 |
| 12000 | 78.76 | 1.07 |
| 13000 | 80.68 | 1.18 |
| 14000 | 83.24 | 1.63 |
| 15000 | 92.38 | 1.60 |
| 15500 | 103.42 | 1.53 |
| 16000 | 98.96 | 1.57 |
| 17000 | 25.44 | 10.62 |







NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp