

HFCG-1760+

 $50\Omega$ 1800 to 8000 MHz

# The Big Deal

- Small size 2.0 mm x 1.25 mm
- Good Power handling
- Ceramic construction



Generic photo used for illustration purposes only CASE STYLE: GE0805C-9

# **Product Overview**

HFCG-1760+ is a high pass filter with passband from 1800 MHz to 8000 MHz supporting a variety of applications. This model provides 2 dB typical insertion loss over a wide band due to strategically constructed layout. Housed in a tiny 0805 ceramic form factor with wraparound terminations, the filter is ideal for dense PCB layouts with minimal performance variation due to parasitics.

# **Key Features**

Feature	Advantages		
Small size, 2.0 mm x 1.25 mm	Accommodates tight space requirements for dense PCB layouts.		
Wrap around termination	Provides excellent solderability and easy visual inspection capability.		
LTCC construction	Provides a rugged package that is well suited for tough environments including high humidity and high temperature extremes.		
Ultra-wide pass band	This filter has a very wide passband from 1.8 GHz to 8 GHz.		

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

1800 to 8000 MHz  $50\Omega$ 

# HFCG-1760+



Generic photo used for illustration purposes only CASE STYLE: GE0805C-9

### +RoHS Compliant

Тур.

Max.

Unit

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Min.


### **Features**


- Small size
- Temperature stable
- LTCC construction
- · Good power handling, 2.5W

## **Applications**

- Transmitters / Receivers
- Test and measurements
- · Military applications
- · Telecommunications and broadband wireless systems

### **Functional Schematic**





Electrical Specifications (1,2) at 25°C

Frequency (MHz)

F#

2 Measured on Mini-Circuits Characterization Test Board TB-1104+


**Parameter** 

Typically, a ±5% frequency deviation from the stated value may occur on a unit-to-unit basis.

Maximum Ratings				
Operating Temperature	-55°C to 125°C			
Storage Temperature	-55°C to 125°C			
RF Power Input*	2.5 W at 25°C			


\*Passband rating, derate linearly to 0.4W at 125°C ambient Permanent damage may occur if any of these limits are exceeded


# **Typical Frequency Response**




# Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)
10	63.72	0.15
100	55.43	0.11
500	42.40	0.27
600	41.06	0.31
800	38.70	0.38
1200	42.83	0.79
1270	30.26	1.07
1330	20.31	1.61
1360	15.99	2.18
1510	3.09	30.97
1560	2.39	15.64
1760	1.31	17.90
1800	1.24	16.98
2000	1.07	12.86
2100	0.98	12.79
2500	0.56	19.67
5200	0.41	14.52
6000	0.58	11.39
7000	0.69	10.41
8000	0.67	10.63







Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.


C. The parts covered by this specification document are subject to Mini-Circuits standard limited to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

### **Pad Connections**

INPUT	1
OUTPUT	3
GROUND	2, 4, 5, 6


Product Marking: LT

### Demo Board MCL P/N: TB-1104+ Suggested PCB Layout (PL-633)



- 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS (RO4350B) WITH DIELECTRIC THICKNESS .020±.0015. COPPER: 1/2 Oz. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
- 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER PATTERN WITH SMOBC (SOLDER MASK OVER BARE COPPER) DENOTES PCB COPPER PATTERN FREE OF SOLDERMASK

## **Outline Drawing**



## Outline Dimensions (inch )

Wt.	G	F	E	D	С	В	Α
grams	.026	.012	.012	.014	.037	.049	.079
.008	0.65	0.30	0.30	0.35	0.95	1.25	2.00

Note: Please refer to case style drawing for details

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp

