Ceramic **High Pass Filter**

50Ω 2900 to 16000 MHz

HFCG-2750+

The Big Deal

- Small size 0.079" X 0.049" X 0.037"
- Good Power handling
- Ceramic construction



Generic photo used for illustration purposes only CASE STYLE: GE0805C-9

Product Overview

HFCG-2750+ is a high pass filter with passband from 2900 MHz to 16000 MHz supporting a variety of applications. This model provides 1 dB typical insertion loss over a wide band due to strategically constructed layout. Housed in a tiny 0805 ceramic form factor with wraparound terminations, the filter is ideal for dense PCB layouts with minimal performance variation due to parasitics.

Key Features

Feature	Advantages
Small size, 0.079" X 0.049" X 0.037"	Accommodates tight space requirements for dense PCB layouts.
Wrap around termination	Provides excellent solderability and easy visual inspection capability.
LTCC construction	Provides a rugged package that is well suited for tough environments including high humidity and high temperature extremes.
Ultra-wide pass band	This filter has a very wide passband from 2.9 GHz to 16 GHz.

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits trandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Ceramic igh Pass Filter

50Ω

Features

Small size

2900 to 16000 MHz

HFCG-2750+



Generic photo used for illustration purposes only CASE STYLE: GE0805C-9

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Unit

• Temperature stable LTCC construction · Good power handling, 4W


Applications

- Transmitters / Receivers
- · Test and measurements
- Military applications
- Telecommunications and broadband wireless systems

Functional Schematic



Typical Frequency Response



HFCG-2750+ INSERTION LOSS (zoomed)

100 9650 1220 FREQUENCY (MHz)

12200

14750

17300



		Rejection Loss	DC-F1	DC - 1000	30	36	-	dB
	Stop Band	Rejection Loss	F1-F2	1000 - 2000	28	34	-	dB
		Freq. Cut-Off	F3 *	2750	-	3.0	-	dB
			F4-F5	2900 - 3100	-	2.0	-	dB
		Insertion Loss	F5-F6	3100 - 3500	-	1.4	2.1	dB
	Pass Band		F6-F7	3500 - 14000	-	1.0	1.6	dB
			F7-F8	14000 - 16000	-	1.0	-	dB
	Beturn Loss	F4-F8	2900 - 16000	-	14	-	dB	

1 This component is not intended to act as a DC block. Please consult with Mini-Circuits for further details

2 Measured on Mini-Circuits Characterization Test Board TB-1125+

* Typically, a ±5% frequency deviation from the stated value may occur on a unit-to-unit basis.


Maximum Ratings				
Operating Temperature	-55°C to 125°C			
Storage Temperature	-55°C to 125°C			
RF Power Input*	4 W at 25°C			

Passband rating, derate linearly to 0.7 W at 125°C ambient Permanent damage may occur if any of these limits are exc

Typical Performance Data at 25°C

Typical Ferrormance Data at 25 0					
Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)			
10	70.91	0.11			
100	56.20	0.13			
500	43.01	0.26			
1000	37.43	0.29			
2000	40.88	0.49			
2190	30.96	0.73			
2320	20.54	1.08			
2670	3.11	10.45			
2700	2.61	13.08			
2750	2.07	18.90			
2900	1.42	29.13			
3000	1.23	28.64			
3100	1.09	38.88			
3500	0.87	17.34			
4000	0.71	16.34			
10000	0.25	17.81			
14000	0.46	14.30			
16000	0.62	20.12			
17500	4.36	3.43			
18000	8.66	1.72			





4550

7100

0

2

4

18

20

2000

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuit's tandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

∭Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B ECO-012606 HFCG-2750+ EDU3686 URJ 220402 Page 2 of 3

High Pass Filter




Pad Connections

INPUT	1
OUTPUT	3
GROUND	2, 4, 5, 6

Product Marking: MA

Demo Board MCL P/N: TB-1125+ Suggested PCB Layout (PL-633)





1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS (R04350B) WITH DIELECTRIC THICKNESS .020±.0015. COPPER: 1/2 Oz. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.

- 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER PATTERN WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES PCB COPPER PATTERN FREE OF SOLDERMASK

Outline Drawing G TYP D TYP REF 4 6 5 INDEX AREA - \mathbb{Z} В Ň t $\overline{\mathcal{N}}$ 3 1 2 F +.004 TYP PAD SHAPE E TYP MAY VARY C±.009

Outline Dimensions (inch)

Α	В	С	D	E	F	G	Wt.
.079	.049	.037	.014	.012	.012	.026	grams
2.00	1.25	0.95	0.35	0.30	0.30	0.65	.008

Note: Please refer to case style drawing for details

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Min-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectived), "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits