HFCN-2502+

THE BIG DEAL

- · Pass Band, 25 to 57 GHz
- Low Insertion Loss, Typ. 1.8 dB
- Return Loss, Typ. 13 dB
- Stop Band Rejection, Typ. 17 dB
- Power Handling, 1W



Generic photo used for illustration purposes only

CASE STYLE: FV1206-12

+RoHS Compliant
The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- Test & Measurement Equipment
- SATCOM
- 5G mmWave Radio Systems

PRODUCT OVERVIEW

HFCN-2502+ is a miniature low temperature co-fired ceramic (LTCC) high pass filter with a 25 to 57 GHz passband supporting a variety of applications. This model provides 1.8 dB typical insertion loss over a wide band due to its rugged monolithic construction. Housed in a tiny 1206 ceramic form factor, the filter is ideal for dense signal chain PCB layouts where it complements MMIC size and performance. The LTCC fabrication process assures minimal RF performance variation while delivering a product that is well suited for environmental extremes of high humidity and temperature.

KEY FEATURES

Feature	Advantages		
Ultra-wide passband	More than an octave bandwidth for wideband applications		
Cost effective	LTCC is a scalable technology that is cost effective due to ease of production in high quantities.		
Small size 1206	Allows for high layout density of circuit boards, while minimizing effects of parasites.		
Surface Mountable	Suitable for very high volume automated assembly process.		

REV. OR ECO-016066 HFCN-2502+ ATHARVA/CP/AM 221223



HFCN-2502+

50Ω 25 to 57 GHz

ELECTRICAL SPECIFICATIONS 1,2 AT 25°C

Para	meter	F#	Frequency (GHz)	Min.	Тур.	Max.	Units
Stop Band Insertion Loss	la continu I con	DC-F1	0.1 - 10.4	_	20.9	_	dB
	insertion Loss	F1-F2	10.5 - 19.2	_	17.2	_	
Pass Band Return Loss	F3-F4	25 - 33.7	_	1.0	1.5		
	Insertion Loss	F4-F5	33.8 - 50	_	1.8	2.5	dB
	F5-F6	50.1 - 57	_	2.8	3.6		
	F3-F4	25 - 33.7	_	16.7	_		
	Return Loss	F4-F5	33.8 - 50	_	13.6	_	dB
		F5-F6	50.1 - 57	_	15.6	_	


^{1.} Measured on Mini-Circuits Test Board TB-HFCN-2502C+ with connectors and feedlines effects de-embedded using 2X Thru IEEE P370 method.

ABSOLUTE MAXIMUM RATINGS


Parameter	Ratings
Operating Temperature	-55°C to +125°C
Storage Temperature	-55°C to +125°C
RF Power Input	1W max.

Permanent damage may occur if any of these limits are exceeded.

TYPICAL FREQUENCY RESPONSE



FUNCTIONAL SCHEMATIC



This component is not intended to act as a DC block. Please consult with Mini-Circuits for further details.
 DC blocking capacitors are required in applications where DC voltage and/or current is present at either input or output ports.



CERAMIC ligh Pass Filter

HFCN-2502+


50Ω 25 to 57 GHz

PIN CONNECTIONS

RF IN	1
RF OUT	2
GROUND	3


PRODUCT MARKING: VK

EVALUATION BOARD MCL P/N: TB-HFCN-2502C+ SUGGESTED PCB LAYOUT (PL-748)




- THICKNESS: .0079±.001; COPPER: HVLP/HVLP. FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.

 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



OUTLINE DRAWING



METALLIZATION

Dimensions are in inches [mm]. Tolerances: 2 Pl.±.01; 3 Pl. ±.005


TAPE & REEL INFORMATION: F75


HFCN-2502+


50Ω 25 to 57 GHz


TYPICAL PERFORMANCE DATA AT 25°C

Frequency (GHz)	Insertion Loss (dB)	Return Loss (dB)
0.1	68.94	0.04
0.5	49.87	0.11
1.0	43.45	0.06
5.0	28.99	0.07
10.4	21.20	0.18
10.5	21.10	0.18
19.2	28.49	0.43
25.0	0.92	20.81
33.7	0.68	22.11
33.8	0.68	22.04
40.0	0.92	27.03
50.0	1.63	24.32
50.1	1.62	24.86
57.0	2.25	32.69
65.0	3.93	9.96









NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html