Surface Mount **Bandpass Filter**

50Ω 145 to 155 MHz

BPF-F150+



The Big Deal

- Narrow bandwidth
- High Rejection
- Good VSWR
- Shielded package

Generic photo used for illustration purposes only CASE STYLE: HP1156

Product Overview

BPF-F150+ is a 50Ω bandpass filter in a shielded package fabricated using SMT technology. This bandpass filter covers from 145 to 155 MHz. This unit uses a miniature high Q capacitors and wire welded inductors for high reliability, It has repeatable performance across production lots and consistent performance across temperature.

Key Features

Feature	Advantages
Narrow bandwidth filter	Narrow bandwidth with fast roll-off, this will attenuate frequencies closer to the passband with good rejection value of > 40 dB which increases selectivity on the adjacent channel
Good rejection	This enables the filter attenuate spurious signals and reject harmonics for broad frequency band.
Shielded package	The small surface mount package enables the BPF-F150+ to used in compact design

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. G. The parts covered by this specification document are subject to Mini-Circuits trandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Surface Mount **Bandpass Filter**

50Ω 145 to 155 MHz


Features

- · Narrow bandwidth
- · Sharper cut-off
- · Shielded package


Applications

- · Radio test equipment
- Receiver \ Transmitter
- Harmonic rejection

Functional Schematic



Typical Frequency Response





Mini-Circuits

Generic photo used for illustration purposes only CASE STYLE: HP1156


Electrical Specifications at 25°C


Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Center Frequency	—	—	—	150	—	MHz
Pass Band	Insertion Loss	F1-F2	145-155	-	6	7	dB
	VSWR	F1-F2	145-155	_	1.58	1.92	:1
Stop Bond Lower	Insertion Loss	DC-F3	DC-133	40	45	—	dB
Stop Band, Lower	VSWR	DC-F3	DC-133	_	20	—	:1
Stop Band, Upper	Insertion Loss	F4-F5	170-1400	40	44	_	dB
	VSWR	F4-F5	170-1400	_	20	—	:1


Maximum Ratings			
Operating Temperature	-40°C to 85°C		
Storage Temperature	-55°C to 100°C		
RF Power Input	1 W		

Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C VSWR (:1) Insertion Loss (dB) Frequency (MHz) Frequency (MHz) **Group Delay** (nsec) 103.38 145.02 106.68 145.0 96.90 63.40 146.11 42.10 145.5 146.0 101.81 97.88 100 130 133 52.70 28.78 146.5 94.67 135 44 47 21.05 147.0 147.5 92 04 29.99 11.09 89.84 138 140 21.46 6.88 148.0 88.05 3.37 1.92 141 12 65 148.5 86 61 142 8.22 149.0 85.46 145 4.52 1.08 149.5 84.56 1.14 1.20 150 3.76 150.0 83 90 155 4.37 150.5 83.48 160 15.64 5.26 151.0 83.31 161 20 47 7 95 151.5 83 35 162 25.04 10.83 152.0 83.67 163 29.25 13.82 152.5 84.28 51.78 85.22 170 36.57 153.0 200 85.49 149.51 153.5 86.54 700 91.01 670.66 154.0 88.25 1400 182.92 155.0 93.28 75.43







Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

∭Mini-Circuits

FREQUENCY (MHz)

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.A M174392 BPF-F150+ EDU2619/1 URJ 180828 Page 2 of 3

BPF-F150+


Bandpass Filter

BPF-F150+

Pad Connections

INPUT		18
OUTPUT		9
GROUND	1,3,4,5,6,7,8,10,12	,13,14,15,16,17
NO CONNEC	TION	2,11


Demo Board MCL P/N: TB-695+ Suggested PCB Layout (PL-418)




NOTES: 1. TRACE WIDTH IS SHOWN FOR OAK-602, WITH DIELECTRIC THICKNESS .022"±.0015". COPPER: 1/2 Oz. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED. 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE. DENOTES PCB COPPER LAYOUT WITH SMOBC (STORES WICK OVER BARE COPPER) (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Outline Drawing





Outline Dimensions (inch)

J	н	G	F	Е	D	С	В	А
.305	.140	.140	.180	.100	.100	.350	1.360	.730
7.75	3.56	3.56	4.57	2.54	2.54	8.89	34.54	18.54
14/4		-	0	-				K
Wt.		R	Q	Р	IN	IVI	L	ĸ
grams		.770	.110	1.400	.275	.120	.225	.150
6.0		19.56	2.79	35.56	6.99	3.05	5.72	3.81

Note: Please refer to case style drawing for details

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Min-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectived), "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits