Surface Mount **Bandpass Filter**

BPF-V1000+

 50Ω 940 to 1060 MHz



Generic photo used for illustration purposes only CASE STYLE: KV1974

The Big Deal

- · Flat group delay
- Steep rejection up to 3000 MHz
- Thin package

Product Overview

The BPF-V1000+ is a 50Ω bandpass filter fabricated using SMT technology. This bandpass filter covers from 940-1060 MHz. It has very low group delay flatness for the committed rejection performance. Equalization had made with in the circuit to achieve this. So that this filter provides sharp rejection with flat group delay in the flat gain requirement application.

Key Features

Feature	Advantages
Low group delay flatness	Can be used in flat gain requirement application
Steep rejection	This enables the filter to attenuate spurious signals near the passband edges and goes up to 3000 MHz
Thin package	Helps to use in the small housing.

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Bandpass Filter

 50Ω 940 to 1060 MHz

BPF-V1000+



Generic photo used for illustration purposes only CASE STYLE: KV1974

Min.

30

30

Тур.

1000

3

1.5

40

10

40

10

Max.

6

2

Unit

MHz

dΒ

ns

dB

:1

dB

:1


Features

- · Flat group delay
- Steep rejection up to 3000 MHz
- · Thin package


Applications

- · Aviation / Aeronautical
- · Radar and Navigation system

Functional Schematic



Typical Frequency Response



+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Stop Band, Lower **VSWR** DC-F3 Insertion Loss F4-F5 Stop Band, Upper **VSWR** F4-F5 **Maximum Ratings** Operating Temperature

VSWR

Parameter

Pass Band

Storage Temperature

RF Power Input

Center Frequency

Group delay flatness

-55°C to 100°C

0.5 W

Insertion Loss

Insertion Loss

ermanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Electrical Specifications at 25°C

F1-F2

F1-F2

F1-F2

DC-F3

Frequency (MHz)

940-1060

940-1060

940-1060


DC-860


DC-860


1140-3000


1140-3000

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1	99.47	192.05	940	11.15
250	87.68	72.29	945	11.05
860	47.17	23.99	950	11.04
880	27.10	12.58	960	11.15
885	22.16	9.85	970	11.31
895	13.22	4.90	975	11.43
905	6.75	1.88	980	11.57
920	3.92	1.25	990	11.80
940	3.43	1.34	995	11.82
1000	3.90	1.05	1000	11.74
1060	4.01	1.36	1005	11.58
1085	9.06	3.30	1010	11.38
1100	17.59	7.90	1015	11.15
1105	20.75	9.66	1020	10.94
1120	30.84	14.93	1025	10.75
1125	34.60	16.70	1030	10.60
1140	49.83	22.00	1035	10.49
2000	81.15	126.29	1040	10.44
2500	76.64	102.68	1050	10.66
3000	58.51	91.68	1060	11.64









Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.


C. The parts covered by this specification document are subject to Mini-Circuits standard limited to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Pad Connections

INPUT	1
OUTPUT	10
GROUND	2,3,4,5,6,7,8,9,11,12,13,14,15,16


Demo Board MCL P/N: TB-953+ Suggested PCB Layout (PL-507)

> SUGGESTED MOUNTING CONFIGURATION FOR KV1974 CASE STYLE, "16FL02" PIN CODE




NOTE:

- 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .060" ± .004"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED. 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Outline Drawing



Outline Dimensions (inch)

Note: Please refer to case style drawing for details

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp