
Coaxial **Precision Fixed Attenuator**

20dB **50**Ω 20W

Maximum Ratings

Operating Temperature	-55°C to 100°C**			
Storage Temperature	-55°C to 100°C			
**85°C with output into open or short. Permanent damage may occur if any of these limits are exceeded.				

Outline Drawing



Outline Dimensions (inch)

А	В	С	D	Е	wt
	1.50		3.04		grams
	38.10		77.22		86.0

DC to 18 GHz

Features

- DC to 18000 MHz
- precise attenuation
- excellent VSWR, 1.30 typ
- stainless steel N male and female connectors

Applications

- matching
- instrumentation
- test set-ups
- · high power measurements





Generic photo used for illustration purposes only CASE STYLE: DC1645 Model Connectors N-Female N-Male BW-N20W20+

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Electrical Specifications at 25°C


Parameter	Condition (GHz)	Min.	Тур.	Max.	Unit
Frequency Range		DC	_	18	GHz
	DC - 18	_	20	_	dB
Attenuation	DC - 12.4	19.25	_	20.75	
	12.4 - 18	19.0		21.0	
	DC - 6	_	_	1.3	:1
VSWR	6 - 12.4	_	_	1.3	
	12.4 - 18	_	—	1.40	
Input Power ¹		_	_	20	W

1. Max. power at 25°C ambient, derate linearly to 4W at 100°C. Peak power 500W max. 5µsec. pulse with, 100Hz PRF.

Typical Performance Data

.,					
	Frequency (GHz)	Attenuation (dB)	VSWR (:1)		
	0.01	19.96	1.00		
	2.0	20.09	1.05		
	4.0	20.07	1.07		
	6.0	20.03	1.06		
	8.0	20.07	1.14		
	10.0	19.86	1.07		
	12.4	20.03	1.06		
	14.0	19.66	1.10		
	16.0	19.48	1.12		
	18.0	19.55	1.13		





A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement ins C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collective). "Standard Terms": Burshearm of this Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Electrical Schematic

