

Engineering Development Model

Level 13 (LO Power +13 dBm)

Frequency Mixer

HJK-ED11067A/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click back, and then click Contact Us for Applications support



CASE STYLE: TTT167

ELECTRICAL SPECIFICATIONS 50Ω @25°C

Parameter	Min.	Typ.	Max.	Units
Frequency	LO/RF			MHz
	IF			MHz
Conversion Loss	600		1000	
	0.3		300	
L-R Isolation		7.6		dB
L-I Isolation		36		dB
IP3		37		dB
		+26		dBm
1 dB Compression		+13		dBm

MAXIMUM RATINGS

Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	+15 dBm

PIN CONNECTIONS

LO	2
RF	1
IF	3
GROUND	4,5,6

Electrical Schematic

