Coaxial **Precision Fixed Attenuator**

50Ω **5W** 30dB

Maximum Ratings

Operating Temperature -55°C to 100°C Storage Temperature -55°C to 100°C** **With mated connectors. Unmated, 85°C max.

Permanent damage may occur if any of these limits are exceeded

Outline Drawing "N" MALE "N" FEMALE CONN B±.01 E A/F -D±.05

Outline Dimensions (inch)

wt	Е	D	В
grams	.812	1.90	.61
49.7	20.62	48.26	15.49

DC to 18000 MHz

Features

- DC to 18000 MHz
- precise attenuation
- excellent VSWR, 1.20 typ
- stainless steel N male and female connectors

Applications

- matching
- instrumentation
- test set-ups





Generic photo used for illustration purposes only CASE STYLE: DC736 Connectors Model N-Female N-Male BW-N30W5+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications

FREQ. RANGE (MHz)		ACCURACY	DC-4 GHz Max.	VSWR ² (:1) 4-8 GHz Max.	8-12.4 GHz Max.	MAX. INPUT POWER ³ (W)
DC-18000	30	±0.85	1.20	1.25	1.30	5

1. At 25°C, accuracy includes frequency and power variations. Temperature coefficient for attenuation: .0004dB/dB/°C typ. 2. VSWR from 12.4 to 18 GHz, 1.6:1 typ.


3. Average power at 25°C ambient, derate linearly to 2W at 100°C. Peak Power 125W max. 5µsec. pulse width, 100 Hz PRF.


Typical Performance Data

Frequency (MHz)	Attenuation (dB)	VSWR (:1)
100	30.02	1.00
2000	30.03	1.02
4000	29.96	1.02
6000	30.02	1.09
8000	29.89	1.06
10000	29.85	1.04
12000	29.87	1.13
14000	29.74	1.10
16000	29.68	1.11
18000	29.59	1.05









A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement ins C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Durcharase of this use

Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. D M151107 EA-8722 BW-N30W5-200504 Page 1 of 1