# **Precision Fixed Attenuator**

BW-S10W5+

 $50\Omega$ 

5W

10dB

DC to 18000 MHz

### **Maximum Ratings**

Operating Temperature -55°C to 100°C Storage Temperature -55°C to 100°C\*\*

\*\*With mated connectors. Unmated, 85°C max.

Permanent damage may occur if any of these limits are exceeded.

### **Features**

- DC to 18000 MHz
- precise attenuation

**Applications** 

 instrumentation • test set-ups

matching

- excellent VSWR, 1.20 typ.
- stainless steel SMA male and female connectors

Generic photo used for illustration purposes only


CASE STYLE: DC737 Connectors Model

SMA Female-SMA Male BW-S10W5+

### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

## **Outline Drawing**



# Outline Dimensions (inch )

В D Е wt .61 1.20 .312 grams 15.49 30.48 7.92 9.1

# **Electrical Specifications**


FREQ. RANGE (MHz)	ATTENUATION <sup>1</sup> (dB)		VSWR <sup>2</sup> (:1)  DC-4 4-8 8-12.4			MAX. INPUT POWER <sup>3</sup> (W)
f <sub>L</sub> -f <sub>U</sub>	Nom.	ACCURACY	GHz Max.	GHz Max.	GHz Max.	
DC-18000	10	±0.60	1.20	1.25	1.30	5


- 1. At 25°C, accuracy includes frequency and power variations. Temperature coefficient for attenuation: .0004dB/dB/°C typ.
- 2. VSWR from 12.4 to 18 GHz, 1.6:1 typ.
- 3. Average power at 25°C ambient, derate linearly to 2W at 100°C. Peak Power 125W max. 5µsec pulse width, 100 Hz PRF.


# **Typical Performance Data**

Frequency (MHz)	Attenuation (dB)	VSWR (:1)
100	9.83	1.01
2000	9.88	1.04
4000	9.87	1.07
6000	9.95	1.12
8000	9.92	1.05
10000	9.92	1.24
12000	9.94	1.13
14000	9.99	1.13
16000	9.95	1.28
18000	10.14	1.20

#### **Electrical Schematic**







A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Ferms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Ferms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp