Coaxial **Precision Fixed Attenuator**


DC to 26 GHz **50**Ω 2W 3dB

Maximum Ratings

Operating Temperature -55°C to 100°C Storage Temperature -55°C to 100°C** **With mated connectors. Unmated, 85°C max.

Permanent damage may occur if any of these limits are exceeded.

Outline Drawing



Outline Dimensions ((inch)
-----------------------------	--------

wt	F	F	П	в
		-	D	Б
grams	.312	.312	.85	.36
4.3	7.92	7.92	21.59	9.14

Electrical Schematic \sim

R3 <

R2

0

FEMALE

0

MALE

 \leq

R1

Features

- DC to 26 GHz
- precise attenuation
- excellent VSWR, 1.08 typ
- stainless steel SMA male and female connectors

Applications

- matching
- instrumentation
- test set-ups





Generic photo used for illustration purposes only

CASE STYLE: FF659 **Connectors** Model SMA-Fem SMA-Male BW-S3-2W263+

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Electrical Specifications at 25°C


Parameter	Condition (GHz)	Min.	Тур.	Max.	Unit
Frequency Range		DC	_	26	GHz
Attenuation ¹	DC - 26	—	3	—	
	DC - 12	2.7	_	3.3	dB
	12 - 18	2.7	-	3.3	
	18 - 26	2.7	—	3.7	
	DC - 12	_	1.07	1.20	
VSWR	12 - 18	_	1.08	1.25	:1
	18 - 26	_	1.17	1.40	
Input Power ²	DC - 26	_	_	2	W

1. At 25°C, accuracy includes frequency and power variations. Temperature coefficient for attenuation: .0004 dB/dB/°C typ. 2. Max. power at 25°C ambient, derate linearly to 0.5W at 100°. Peak power 125W max. 5µsec. pulse width, 100Hz PR

Typical Performance Data

Frequency (GHz)	Attenuation (dB)	VSWR (:1)
0.01	2.79	1.00
1.0	2.82	1.01
4.0	2.84	1.03
8.0	2.88	1.05
10.0	2.90	1.03
12.0	2.92	1.05
14.0	2.95	1.06
16.0	2.99	1.02
18.0	3.03	1.05
20.0	3.09	1.11
26.0	3.28	1.07





A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement ins C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collective). "Standard Terms": Burshearm of this interview.

Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B M151107 BW-S3-2W263+ MD/TH/CP/AM 200527 Page 1 of 1